product data sheet

item no. 73.326.4028.0

bottom BAS GUT GX 16H A

Bottom-base revos basic made of aluminum, with double locking lever forterminal adapters mounted on the rear, open, high version, 16-poles

item no.	73.326.4028.0
EAN	4015573229419
order unit	1 piece(s)

certificates / approvals

technical data

general

housing material	aluminum
color	grey
surface	with powder coating
degree of protection (IP)	IP54
UV resistant	yes
inflammability class of insulation material acc. with UL94	other
operating temperature range min.	-40 °C
operating temperature range max.	120 °C

model

construction	16
model of the housing	equipment mounted (feed-through)
locking mechanism	double locking levers
cable entry	none
type of cable	none
with cable screw gland	no
thread size PG	
hinged lid	no
EMC-version	no
length	113 mm
width	43 mm
height	27.9 mm