
product data sheet

item no. 76.338.6435.1

bottom BAS GUT GL 24HM40 A1

Bottom-base revos basic made of aluminum, with single locking lever andthreaded hole M40 on the right and left side, low version, 24-poles



item no.	76.338.6435.1
EAN	4015573842205
order unit	1 piece(s)

certificates / approvals

technical data

general

housing material	aluminum
color	grey
surface	with powder coating
UV resistant	yes
inflammability class of insulation material acc. with UL94	other
operating temperature range min.	-40 °C
operating temperature range max.	120 °C

model

construction	24H
model of the housing	surface mounting (base)
locking mechanism	single locking lever
cable entry	two-sided
type of cable	thread
with cable screw gland	no
thread size M	40
thread size PG	
hinged lid	no
EMC-version	no
length	144 m
width	57 m
height	80 m