
product data sheet

item no. 71.440.1637.1

# bottom BAS GUM GR 16 M25 B1

Bottom-base revos basic metal-series without coating, with single locking lever and threaded hole M25 on the right and the left side, with protective cover, low version, 16-polig



| | |
|---|---|
| item no. | 71.440.1637.1 |
| EAN | 4049088350672 |
| order unit | 1 piece(s) |

## certificates / approvals

## technical data


**general**


| | |
|---|---|
| housing material | aluminum |
| color | grey |
| surface | bare |
| degree of protection (IP) | IP66 |
| UV resistant | yes |
| inflammability class of insulation material acc. with UL94 | other |
| operating temperature range min. | -40 °C |
| operating temperature range max. | 120 °C |


**model**

| | |
|---|---|
| construction | 16 |
| model of the housing | surface mounting (base) |
| locking mechanism | single locking lever |
| cable entry | two-sided |
| type of cable | thread |
| with cable screw gland | no |
| thread size M | 25 |
| thread size PG | |
| hinged lid | yes |
| EMC-version | no |
| length | 117 mm |
| width | 57 mm |
| height | 57 mm |

technical drawing







These dimensions will be especially checked at delivery
Only inspection dimensions
With /E marked dimensions are only valid for internal use

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit /E gekennzeichnete Maße sind nur für interne Zwecke gültig

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.

| | | |
|---|---|---|
| 71.440.1637.1 | BAS GUM GR 16 M25 B1 | Gewindebohrung /Thread hole |
| Bestellnummer /Order number | Typ /Type | Varianten /Variants |
| Weitere Daten siehe KATALOG oder eKatalog. Additional data see CATALOG or eCatalog. | | www.wieland-electric.com eshop.wieland-electric.com |




Bohrbild /Cut out

Tolerierung Size ISO 14405 Ⓔ / Tolerance system Size ISO 14405 Ⓔ. (This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020 010 ist einzuhalten. Conformity with Wieland document WN 5020 010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance

CAD - Zeichnung, keine manuellen Änderungen CAD - drawing, no manual modifications allowed

1. Verwendung: First Use:

Blatt: Sheet: 1 von of

Werkstoff / Material: Aluminium

Maßstab / Scale: 1:2

Vol.. --- mm³ Obfl./Surf. --- mm²

| | Tag/Date | Name |
|---|---|---|
| gezeichnet drawn | 11.05.2016 | Lunz S |
| geprüft checked | | |
| Normgeor. Stand. check | | |

Zeichnung Nr. / Drawing No.: 71.440.1637.1 13K

Index

Maße in mm / Dimensions are in mm

Ersatz für / Replacement for:

Index | Datum / Blatt Date / Sheet | Änderung / Revision

wieland www.wieland-electric.com

Type: revos BASIC M

Bennenung/Title: GEHAEUSEUNTERTEIL

Baugröße 16 mit Klappdeckel-Kabelabgang 2x M25

Housing size 16 with protective cover-cable outlet 2x M25