product data sheet

item no. 70.441.0637.1

bottom BAS GUM GS 6 M20 B1

Bottom-base revos basic metal-series without coating, with single locking lever and threaded hole M20 on the left side, with protective cover, low version, 6-polig



item no.	70.441.0637.1
EAN	4049088365102
order unit	1 piece(s)

certificates / approvals

technical data


general


housing material	aluminum
color	grey
surface	bare
degree of protection (IP)	IP66
UV resistant	yes
inflammability class of insulation material acc. with UL94	other
operating temperature range min.	-40 °C
operating temperature range max.	120 °C


model

construction	6
model of the housing	surface mounting (base)
locking mechanism	single locking lever
cable entry	sideways
type of cable	thread
with cable screw gland	no
thread size M	20
thread size PG	
hinged lid	yes
EMC-version	no
length	84 mm
width	52 mm
height	74.6 mm

technical drawing








These dimensions will be especially checked at delivery
Only inspection dimensions
With /E marked dimensions are only valid for internal use

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit /E gekennzeichnete Maße sind nur für interne Zwecke gültig

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.

70.44[5]1.0637.1	BAS GUM GS 6 M25/M20 B1	Gewindebohrung /Thread hole
Bestellnummer /Order number	Typ /Type	Varianten /Variants
Weitere Daten siehe KATALOG oder eKatalog. Additional data see CATALOG or eCatalog.		www.wieland-electric.com eshop.wieland-electric.com



Bohrbild
/Cut out

Tolerierung Size ISO 14405 Ⓔ / Tolerance system Size ISO 14405 Ⓔ.
(This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020 010 ist einzuhalten. Conformity with Wieland document WN 5020 010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance

CAD - Zeichnung, keine manuellen Änderungen CAD - drawing, no manual madifications allowed

1. Verwendung: First Use:

Blatt: Sheet: 1 von of

Werkstoff / Material: Aluminium

Maßstab / Scale: 1:2

Vol.. --- mm³ Obfl./Surf. --- mm²

	Tag/Date	Name
gezeichnet drawn	19.05.2016	Lunz S.
geprüft checked		
Normgeor. Stand. check		

Zeichnung Nr. / Drawing No.: T 70.441.0637.1 13K

Index

Maße in mm / Dimensions are in mm

Ersatz für / Replacement for:

Index | Datum / Blatt Date / Sheet | Änderung / Revision

wieland
www.wieland-electric.com

Type: revos BASIC M

Bennenung/Title: GEHAEUSEUNTERTEIL

Baugröße 6 mit Klappdeckel-Kabelabgang 1x M20/M25

Housing size 6 with protective cover-cable outlet 1x M20/M25