product data sheet

item no. 97.041.4053.1

connector RST50I4S B1 ZR5 S SW

RST® POWER connector, straight, number of poles 4, female, connection type screw connection, rated voltage 250 V / 400 V, rated current 50 A, cable diameter 15 - 25 mm, color of coding/ contact carrier black



item no.	97.041.4053.1
EAN	4049088070518
order unit	20 piece(s)

certificates / approvals

technical data

note

note	fine-stranded and stranded wires have to be used without ferrules

general

rated current	50 A
rated voltage	250 V / 400 V
rated impulse voltage	4 kV
strain relief	yes
pollution degree	3
lockable	yes
color of coding/ contact carrier	black
marking of poles	1, 2, 3, PE
color of housing inclusive strain relief	black
RAL-Nummer Codierung/Kontakteinsatz	9005

connection data

cable diameter max.	25 mm
cable diameter min.	15 mm
connection cross section solid mm² max.	6 mm²
connection cross section solid mm² min.	4 mm²
connection cross section fine stranded mm² max.	16 mm²
connection cross section fine stranded mm² min.	4 mm²
terminations per pole	1
connection cross section stranded mm² min.	4 mm²
connection cross section stranded mm² max.	6 mm²
sheath strip length	80 mm
wire strip length	10 mm

model

model	female
connection type	screw connection
degree of protection (IP)	IP66/IP67/IP69

material

housing material	polyamide
halogen free	yes
contact material	CuZn
fire load	0.407 kWh/St
surface finish	silver-plated


dimensions


length	145 mm
width	65 mm
height	65 mm

assembly


item no.	type	description
97.042.5553.1	device connector RST50I4S S1 ZM02V SW	RST® POWER device connector, standard, straight, fixed in position, M32, number of poles 4, model male, connection type screw connection, rated voltage 250 V / 400 V, rated current 50 A, color of coding/ contact carrier black

technical drawing





Auslieferungszustand
delivery status
(1:2)




für Kabeldurchm. 15-25mm
for cable diameter 15-25mm


Farbe: schwarz,
ähnl. RAL9005
color: black,
similar to RAL9005

Farbe: schwarz,
ähnl. RAL9005
color: black,
similar to RAL9005

Verpackungseinheit: je 20 Stück
packaging unit: per 20

A-A





Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.

Anschlussart: Schraub
Anschlussquerschnitt: ein-/ mehrdrähtig: 4-6 mm² / feindrähtig: 4*-16 mm²
connection type: screw
cross section: solid/ stranded: 4-6 mm² / flexible: 4*-16 mm²

* Leiter 4 mm² flexibel nur in Verbindung mit Aderendhülsen.
Conductor flexible 4 mm² only by using of end sleeves.

Type: RST50i4S B1 ZR5 S SW

50 A/250 V/400 V/4 kV/2
IP66/67

Tolerierung nach DIN 7167/Tolerance system acc. to DIN 7167.
(This DIN-standard desbribes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach UU-TOM-05/03 ist einzuhalten. Conformity with Wieland document UU-TOM-05/03 (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach / General tolerance

CAD - Zeichnung, keine manuellen Änderungen / CAD - drawing, no manual modifications allowed

1.Verwendung: - / First Use: -

Blatt: 1 von 1 / Sheet: 1 of 1

Werkstoff/Material	2012	Tag/Date	Name	Zeichnung Nr./Drawing No.	Index
	gezeichnet / drawn	17.02.	Bratkorb	97.041.4053.1 01K	
Maßstab/Scale 1:1	geprüft / checked	-	-		
	Normgepr. Stand. check	-	-	Maße in mm/Dimensions are in mm	
Vol. mm³ Oft./Surf. mm²	Ersatz für/Replacement for: -				

wieland
Elektrische Verbindungen

Type

Benennung/Title: ERSTANSCHLUSS_BU_KOMPLETT

Index | Datum / Blatt / Date / Sheet
Änderung/Revision

DU-PEM-08/91a

97041405310IK_2 CADW2028 hollet 2012-05-24107:55:13 1:000