product data sheet

item no. X6.052.4153.9

connector RST20I5SXS1 ZR2SV BL07

RST20i5 ATEX Connector, straight, number of poles 5, male, connection type screw connection, rated voltage 250 V / 400 V, rated current 20 A, cable diameter 10 - 14 mm, color of coding/ contact carrier light blue



item no.	X6.052.4153.9
EAN	4049088009648
order unit	100 piece(s)

certificates / approvals

SEV-Ex

technical data

note

note	fine-stranded and stranded wires have to be used without ferrules

general

rated current	20 A
rated voltage	250 V / 400 V
rated impulse voltage	4 kV
strain relief	yes
pollution degree	3
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	light blue
marking of poles	1, 2, 3, 4, 5
color of housing inclusive strain relief	black
explosion-tested version	yes

connection data

cable diameter max.	14 mm
cable diameter min.	10 mm
connection cross section solid mm² max.	2.5 mm²
connection cross section solid mm² min.	1.5 mm²
connection cross section fine stranded mm² max.	2.5 mm²
connection cross section fine stranded mm² min.	1.5 mm²
terminations per pole	1
sheath strip length	26.5 mm
wire strip length	8 mm

model

model	male
connection type	screw connection
degree of protection (IP)	IP66/68 (3m;2h) /IP69

material

housing material	polyamide
halogen free	yes
contact material	CuZn
fire load	0.286 kWh
insulation components continous temperature	100 °C
surface finish	silver-plated

dimensions

length	78.4 mm
width	34.6 mm
height	34.6 mm

accessories

item no.	type	description
05.565.9953.1	cover for male connector SW	RST20i5/4 cover piece, for covering unused male connectors, color black
99.532.0000.7	cover for male connector SW	RST20i5/4 cover piece, for covering unused male connectors, with fastening belt, color black

assembly

item no.	type	description
X6.051.5053.9	device connector RST20I5SXB1 M01 BL04	RST20i5 ATEX Device connector, standard, straight, M25, number of poles 5, model female, connection type screw connection, rated voltage 250 V / 400 V, rated current 20 A, color of coding/ contact carrier light blue
X6.051.4153.9	connector RST20I5SXB1 ZR2S BL07	RST20i5 ATEX Connector, straight, number of poles 5, female, connection type screw connection, rated voltage 250 V / 400 V, rated current 20 A, cable diameter 10 - 14 mm, color of coding/ contact carrier light blue