product data sheet

item no. 96.042.4951.4

connector RST20I4S S1 ZASSVL BR01

RST20i4 Connector, straight, number of poles 4, male, connection type screw connection, rated voltage 50 V / 120 V, rated current 20 A, AS-i profile cable, color of coding/ contact carrier signal brown



item no.	96.042.4951.4
EAN	4049088031540
order unit	100 piece(s)

certificates / approvals

technical data

note

note	RST® terminals with screw clamping allow the connection of conductors without special preparation (without ferrules) according to EN 60999-1.

general

rated current	20 A
rated voltage	50 V / 120 V
rated impulse voltage	4 kV
strain relief	yes
pollution degree	3
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	signal brown
marking of poles	1, 2, 3, 4
color of housing inclusive strain relief	black

connection data

cable diameter max.	10 mm
cable diameter min.	4 mm
connection cross section solid mm² max.	4 mm²
connection cross section solid mm² min.	0.75 mm²
connection cross section fine stranded mm² max.	4 mm²
connection cross section fine stranded mm² min.	0.75 mm²
terminations per pole	1
special cable geometry	AS-i profile cable
connection cross section stranded mm² min.	0.75 mm²
connection cross section stranded mm² max.	4 mm²
sheath strip length	26.5 mm
wire strip length	8 mm

model

model	male
connection type	screw connection

degree of protection (IP)	IP66/68 (3m;2h) /IP69

material

housing material	polyamide
halogen free	yes
contact material	CuZn
fire load	0.288 kWh
insulation components continous temperature	100 °C
surface finish	silver-plated

dimensions

length	79.9 mm
width	34.6 mm
height	34.6 mm


accessories


item no.	type	description
05.565.9953.1	cover for male connector SW	RST20i5/4 cover piece, for covering unused male connectors, color black
99.532.0000.7	cover for male connector SW	RST20i5/4 cover piece, for covering unused male connectors, with fastening belt, color black


assembly

item no.	type	description
96.043.6051.4	device connector RST20I4S B1 M00 B BR06	RST20i5/4 device connector (90° angled) M20, 4 pole, female, screw connection, modular, application ~50V/-120V, 20A, coding color signal brown, color of housing black
96.041.5051.4	device connector RST20I4S B1 M01 L BR01	RST20i4 Device connector, standard, straight, M25, number of poles 4, model female, connection type screw connection, rated voltage 50 V / 120 V, rated current 20 A, color of coding/ contact carrier signal brown
96.041.6051.4	device connector RST20I4S B1 M00 L BR01	RST20i4 Device connector, modular, straight, M20, number of poles 4, model female, connection type screw connection, rated voltage 50 V / 120 V, rated current 20 A, color of coding/ contact carrier signal brown
96.043.6251.4	device connector RST20I4S B1 M91 LBR01	RST20i4 Device connector, modular, angled 90°, M25, number of poles 4, model female, connection type screw connection, rated voltage 50 V / 120 V, rated current 20 A, color of coding/ contact carrier signal brown
96.041.4951.4	connector RST20I4S B1 ZASS L BR01	RST20i4 Connector, straight, number of poles 4, female, connection type screw connection, rated voltage 50 V / 120 V, rated current 20 A, AS-i profile cable, color of coding/ contact carrier signal brown
96.045.6151.4	device connector RST20I4S B1 M13 B BR06	RST20i5/4 device connector (7° angled) M16, 4 pole, female, screw connection, modular, application ~50V/-120V, 20A, coding color signal brown, color of housing black
96.041.6151.4	device connector RST20I4S B1 M03 L BR06	RST20i5/4 device connector M16, 4 pole, female, screw connection, modular, application ~50V/-120V, 20A, coding color signal brown, color of housing black
96.040.0151.4	distributor RST20I4B 3P1 F VGB BR06	RST20i4 Distributor, parallel connection, with fastening option, number of poles 4, rated voltage 50 V / 120 V, rated current 20 A, number of inputs 1, number of outputs 3, color of coding/ contact carrier signal brown


technical drawing









Auslieferungszustand
delivery status



Verpackungseinheit: 100 Stück
packaging unit: 100 pcs





Typ: RST2014S S1 ZASSVL BR01

Tolerierung nach DIN 7167/Tolerance system acc. to DIN 7167.
[This DIN-standard desbribes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances].

nein/no ☒ Stoffverbots- und Deklarationsliste nach OU-TGM-05/03 ist einzuhalten.
Conformity with Wieland document OU-TGM-05/03 [list of prohibited / declarable hazardous substances] to be declared!

Freitoleranz nach / General tolerance

CAD - Zeichnung, keine manuellen Änderungen / CAD - drawing, no manual modifications allowed

1.Verwendung: - / First Use: -

Blatt/Sheet: 1 von/of 1

Werkstoff/Material		2008	Tag/Date	Name	Zeichnung Nr./Drawing No.		Index
		gezeichnet/drawn	08.08.	Schwabbauer	96.042.4951.4 01K		
Maßstab/Scale 1:1		geprüft/checked	-	-			
		Normgep. Stand./check	-	-	Maße in mm/Dimensions are in mm		
Vol. mm³	Ofl./Surf. mm²	Ersatz für/Replacement for: -					
wieland Elektrische Verbindungen		Type	Benennung/Title: STECKERTEIL_MIT_ZUGENTLASTUNG male connector with cord grip for AS-I cable Schraubanschluss ohne Drahtschutz/screw connection without wire protection Kodierung/ coding 1 (Niedervolt/low voltage)				
Index	Datum / Blatt Date / Sheet	Änderung/Revision					

OU-PEM-08/91

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.

These dimensions will be especially checked at delivery
Only inspection dimensions
With Æ marked dimensions are only valid for internal use
Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit Æ gekennzeichnete Maße sind nur für interne Zwecke gültig

96042495140IK_4 CADW1024 Schwabbauer 2008-08-08T14:07:52 1.000