product data sheet

item no. 99.906.0000.7

distributor RST20I3B 3P1 F VG SW

RST® CLASSIC compact distributor 1I / 3O, rated voltage 250 V, rated current 20 A, number of poles 3, degree of protection (ip) IP66/68 (3m 2h) /IP69, number of inputs 1, number of outputs 3, pole codification L, N, PE, color of coding/ contact carrier black, ral number coding/contact insert



item no.	99.906.0000.7
EAN	4015573971288
order unit	1 piece(s)

certificates / approvals

technical data

general

rated current	20 A
rated voltage	250 V
rated impulse voltage	4 kV
pollution degree	3
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	black
color of separate housing (only for modular versions)	black
color of separate adapter (if present)	black
Pole codification	L, N, PE
RAL number coding/contact insert	9005

model

number of inputs	1
number of outputs	3
type of fastening	yes
degree of protection (IP)	IP66/68 (3m;2h) /IP69
type of distributor	compact distributor

material

housing material	polyamide
halogen free	yes
contact material	CuZn
fire load	1.927 kWh/St
insulation components continous temperature	100 °C
surface finish	silver-plated

dimensions

length	162 mm
width	104 mm
height	57.2 mm

assembly

item no.	type	description

99.712.0000.7	cable assembly RST20I3K1BF 15 15SW	RST® CLASSIC mains connection cable, female - SchuKo plug, number of poles 3, rated voltage 250 V, rated current 16 A, cable type H07RN-F, total length 1.5 m, nominal cross section conductor 1.5 mm², color of coding/ contact carrier black