product data sheet

item no. 46.452.0550.6

cable assembly RST16I5KSBS 15G 05TB04

RST® MINI connecting cable, female - male, number of poles 5, rated voltage 250 V, rated current 16 A, cable type H07RN-F - Enhanced Version, total length 0.5 m, nominal cross section conductor 1.5 mm², color of coding/ contact carrier turquoise blue



item no.	46.452.0550.6
EAN	4049088361975
order unit	50 piece(s)

certificates / approvals

technical data

note

note	The total length may vary up to + / - 3 %.

general

rated current	16 A
rated voltage	250 V
rated impulse voltage	4 kV
pollution degree	3
continuity resistor	7.2 mOhm
lockable	self-locking (unlocking by hand)
color of coding/ contact carrier	turquoise blue
Pole codification	L, N, PE, 1, 2
color of housing inclusive strain relief	black

model

type of construction	cable screw gland
connection type	screw connection
nominal cross section conductor	1.5 mm²
degree of protection (IP)	IP66/68 (3m;2h) /IP69
cable type	H07RN-F - Enhanced Version
cable color	black
cable diameter min.	11.2 mm
cable diameter max.	12.2 mm
version of cable	female - male
type of cord set	connecting cable
version cable end 1	female
version cable end 2	male

shielded	no

material

surface finish	silver-plated
halogen free	yes
insulation components continous temperature	100 °C
fire load	0.876 kWh/St

dimensions

total length	0.5 m