product data sheet

item no. 46.032.4550.4

# connector RST16I3 S S1 ZT4S L BR

RST® MINI connector, straight, number of poles 3, male, connection type screw connection, rated voltage 50 V / 120 V, rated current 16 A, cable diameter 5 - 10.6 mm, color of coding/ contact carrier signal brown



| | |
|---|---|
| item no. | 46.032.4550.4 |
| EAN | 4049088279188 |
| order unit | 100 piece(s) |

## certificates / approvals

## technical data

**note**

| | |
|---|---|
| note | RST® terminals with screw clamping allow the connection of conductors without special preparation (without ferrules) according to EN 60999-1. |

**general**

| | |
|---|---|
| rated current | 16 A |
| rated voltage | 50 V / 120 V |
| rated impulse voltage | 4 kV |
| strain relief | yes |
| pollution degree | 3 |
| lockable | self-locking (unlocking by hand) |
| color of coding/ contact carrier | signal brown |
| Pole codification | 1, 2, 3 |
| color of housing inclusive strain relief | black |
| RAL-Nummer Codierung/Kontakteinsatz | 8002 |

**connection data**

| | |
|---|---|
| cable diameter max. | 10.6 mm |
| cable diameter min. | 5 mm |
| connection cross section solid mm² max. | 2.5 mm² |
| connection cross section solid mm² min. | 0.25 mm² |
| connection cross section fine stranded mm² max. | 2.5 mm² |
| connection cross section fine stranded mm² min. | 0.25 mm² |
| terminations per pole | 1 |
| sheath strip length | 25 mm |
| wire strip length | 8 mm |

**model**

| | |
|---|---|
| model | male |
| connection type | screw connection |
| degree of protection (IP) | IP66/68 (3m;2h) /IP69 |

**material**

| | |
|---|---|
| housing material | polyamide |
| halogen free | yes |
| contact material | CuZn |
| fire load | 0.131 kWh/St |
| insulation components continous temperature | 100 °C |
| surface finish | silver-plated |

**dimensions**

| | |
|---|---|
| length | 64 mm |
| width | 19.9 mm |
| height | 19.9 mm |

## accessories

| item no. | type | description |
|---|---|---|
| 06.563.8853.1 | cover for male connector SW | RST16i3/2 cover piece, for covering unused male connectors, color black |
| 06.563.8953.1 | cover for male connector SW | RST16i3/2 cover piece, for covering unused male connectors, with fastening belt, color black |

## assembly

| item no. | type | description |
|---|---|---|
| 46.031.5050.4 | device connector RST16I3 S B1 M02 L BR | RST® MINI device connector, standard, straight, M16, number of poles 3, model female, connection type screw connection, rated voltage 50 V / 120 V, rated current 16 A, color of coding/ contact carrier signal brown |
| 46.030.1250.4 | distributor RST16I3V 2P1 TGVGL BR | RST® MINI distribution block 1I / 2O, rated voltage 50 V / 120 V, rated current 16 A, number of poles 3, degree of protection (ip) IP66/68 (3m 2h) /IP69, number of inputs 1, number of outputs 2, pole codification 1, 2, 3, color of coding/ contact carrier signal brown, ral number coding/ contact i |

technical drawing

## Kodierung
/Coding



C1


C2


C3


C4



C5





Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit ⌀ gekennzeichnete Maße sind nur für interne Zwecke gültig

These dimensions will be especially checked at delivery
Only inspection dimensions
With ⌀ marked dimensions are only valid for internal use

## Auslieferungszustand
delivery condition





Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.

| | | | |
|---|---|---|---|
| 46.032.4550.6 | RST1613 S S1 ZT4S A TB | C5 | türkisblau /turquoise blue |
| 46.032.4553.9 | RST1613 S S1 ZT4S H BL | C4 | lichtblau /light blue |
| 46.032.4550.4 | RST1613 S S1 ZT4S L BR | C3 | signalbraun /signal brown |
| 46.032.4555.7 | RST1613 S S1 ZT4S GN | C2 | laubgrün /leaf green |
| 46.032.4553.1 | RST1613 S S1 ZT4 SW | C1 | schwarz /black |
| 46.032.4553.0 | RST1613 S S1 ZT4 GL | C1 | lichtgrau /light grey |
| Bestellnummer /Order number | Typ /Type | Kodierung /Coding | |

(a)

**Weitere Daten siehe KATALOG oder eKatalog. Additional data see CATALOG or eCatalog.**
**www.wieland-electric.com eshop.wieland-electric.com**

Tolerierung Size ISO 14405Ⓔ/Tolerance system Size ISO 14405Ⓔ. (This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten. Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance

CAD - Zeichnung, keine manuellen Änderungen CAD - drawing, no manual modifications allowed

1.Verwendung: First Use: -

Blatt: Sheet: 1 von of 1

Werkstoff/Material

Maßstab/Scale 1:1

Vol. mm³ Ofl./Surf. mm²

| | 2014 | Tag/Date | Name |
|---|---|---|---|
| gezeichnet drawn | | 02.09. | Treschan |
| geprüft checked | | - | - |
| Normgepr. Stand. check | | - | - |

Zeichnung Nr./Drawing No. T 46.032.4553.0 13K Index a

Maße in mm/Dimensions are in mm

Ersatz für/Replacement for: -

| Index | Datum / Blatt Date / Sheet |
|---|---|
| a | 06.10.2014/ |

Änderung/Revision

wieland
www.wieland-electric.com

Type RST16..

Benennung/Title

# STECKERTEIL

FA - mit Zugentlastung, 3-polig
male with strain relief 3 poles

460324553013K_2 CADW3025 Ritter 2014-10-06T11:46:27 12000

QU-MEE-01/14 -