product data sheet

item no. 46.030.0155.7

distributor RST16I3B 3P1 FGVG GN

RST® MINI compact distributor 1I / 3O, rated voltage 250 V / 400 V, rated current 16 A, number of poles 3, degree of protection (ip) IP66/68 (3m 2h) /IP69, number of inputs 1, number of outputs 3, pole codification 1, 2, PE, color of coding/ contact carrier leaves green, ral number coding/contact



item no.	46.030.0155.7
EAN	4049088344848
order unit	1 piece(s)

certificates / approvals

technical data

general

rated current	16 A
rated voltage	250 V / 400 V
rated impulse voltage	4 kV
pollution degree	3
lockable	self-locking (unlocking by hand)
color of coding/ contact carrier	leaves green
color of separate housing (only for modular versions)	black
Pole codification	1, 2, PE
RAL number coding/contact insert	6002

model

number of inputs	1
number of outputs	3
type of fastening	yes
degree of protection (IP)	IP66/68 (3m;2h) /IP69
type of distributor	compact distributor

material

housing material	polyamide
halogen free	yes
contact material	CuZn
fire load	1.654 kWh/St
insulation components continous temperature	100 °C
surface finish	silver-plated

dimensions

length	159.6 mm
width	104 mm
height	57.2 mm

accessories

item no.	type	description
06.563.8653.1	cover for female connector SW	RST16i3/2 cover piece, for covering unused female connectors, color black
06.563.8753.1	cover for female connector SW	RST16i3/2 cover piece, for covering unused female connectors, with fastening belt, color black
06.563.8853.1	cover for male connector SW	RST16i3/2 cover piece, for covering unused male connectors, color black
06.563.8953.1	cover for male connector SW	RST16i3/2 cover piece, for covering unused male connectors, with fastening belt, color black