product data sheet

item no. G5.536.0203.3

distributor MST20I3V 2P1S25 02 WSC3

METALYNX² T-distributor, with mounting option, SPUR (tap off fused with 10 A), number of poles 3, rated voltage 250 V, rated current 20 A, number of inputs 1, number of outputs 2, color of coding/ contact carrier white

item no.	G5.536.0203.3
EAN	4049088311543
order unit	20 piece(s)

certificates / approvals

technical data

general

rated current	20 A
rated voltage	250 V
rated impulse voltage	4 kV
pollution degree	2
mechanical coding	code 3
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	white
Pole codification	L, N, PE
RAL number coding/contact insert	9016

lead

model	spur
microfuse (6,3x25 mm)	10 A
drop	sheathed cable LSOH
no. of poles on drop	3
cross section of drop	2.5 mm²
termination of drop	free end
length of drop	2 m
lenght of open end	2 m
stripping length of drop	10 mm
design of conductor ends	ultrasonically compressed wire ends
color of the coding pin	white (C3)
wiring system	
internal cross secction	4 mm²

model

number of inputs	1
number of outputs	2
type of fastening	yes
degree of protection (IP)	IP20
type of distributor	spur

material

housing material	polyamide
halogen free	yes
contact material	CuZn
fire load	0.72 kWh/St

insulation components continous temperature	100 °C
surface finish	silver-plated