product data sheet

item no. G5.441.1304.2

# cable assembly MST20I4KC-S 40 130TBC2

METALYNX² connection cable, male - free end, number of poles 4, rated voltage 250 V, rated current 25 A, cable type metal conduit 16 mm, fire class Eca, total length 13 m, nominal cross section conductor 4 mm², color of coding/ contact carrier turquoise blue

| | |
|---|---|
| item no. | G5.441.1304.2 |
| EAN | 4049088262418 |
| order unit | 3 piece(s) |

## certificates / approvals

## technical data

**general**

| | |
|---|---|
| rated current | 25 A |
| rated voltage | 250 V |
| rated impulse voltage | 4 kV |
| pollution degree | 2 |
| mechanical coding | code 2 |
| lockable | self-locking (unlocking by tool) |
| color of coding/ contact carrier | turquoise blue |
| Pole codification | 2, N, PE, 1 |
| color of housing inclusive strain relief | black |

**lead**

| | |
|---|---|
| model | metal conduit 16 mm |
| inner cores | single cores LSOH |
| single cores | H07Z-R |
| color of the coding pin | turquoise blue (C2) |

**model**

| | |
|---|---|
| nominal cross section conductor | 4 mm² |
| degree of protection (IP) | IP20 |
| wire strip length | 10 mm |
| sheath strip length | 200 mm |
| preparation of conductor ends | tin-plated |
| cable type | metal conduit 16 mm |
| version of cable | male - free end |
| type of cord set | connection cable |
| version cable end 1 | free end |
| version cable end 2 | MST25i4 plug |

**dimensions**

| | |
|---|---|
| total length | 13 m |