product data sheet

item no. G5.441.2003.4

# cable assembly MST20I4KC-S 25 200TRC4

METALYNX² connection cable, male - free end, number of poles 4, rated voltage 250 V / 400 V, rated current 20 A, cable type metal conduit 16 mm, fire class Eca, total length 20 m, nominal cross section conductor 2.5 mm², color of coding/ contact carrier red

| | |
|---|---|
| item no. | G5.441.2003.4 |
| EAN | 4049088275111 |
| order unit | 2 piece(s) |

## certificates / approvals

c UL us LISTED

## technical data

**general**

| | |
|---|---|
| rated current | 20 A |
| rated voltage | 250 V / 400 V |
| rated impulse voltage | 4 kV |
| pollution degree | 2 |
| mechanical coding | code 4 |
| lockable | self-locking (unlocking by tool) |
| color of coding/ contact carrier | red |
| Pole codification | 2, N, PE, 1 |
| color of housing inclusive strain relief | black |

**lead**

| | |
|---|---|
| model | metal conduit 16 mm |
| inner cores | single cores LSOH |
| single cores | H07Z-R |
| color of the coding pin | red (C4) |

**model**

| | |
|---|---|
| nominal cross section conductor | 2.5 mm² |
| degree of protection (IP) | IP20 |
| wire strip length | 10 mm |
| sheath strip length | 200 mm |
| preparation of conductor ends | tin-plated |
| cable type | metal conduit 16 mm |
| version of cable | male - free end |
| type of cord set | connection cable |
| version cable end 1 | free end |
| version cable end 2 | MST20i4 plug |

**dimensions**

| | |
|---|---|
| total length | 20 m |