product data sheet

item no. G5.431.1103.3

cable assembly MST20I3KC-S 25 110WSC3

METALYNX² connection cable, male - free end, number of poles 3, rated voltage 250 V, rated current 20 A, cable type metal conduit 16 mm, fire class Eca, total length 11 m, nominal cross section conductor 2.5 mm², color of coding/ contact carrier white

item no.	G5.431.1103.3
EAN	4049088181399
order unit	3 piece(s)

certificates / approvals

c UL us LISTED

technical data

general

rated current	20 A
rated voltage	250 V
rated impulse voltage	4 kV
pollution degree	2
mechanical coding	code 3
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	white
Pole codification	L, N, PE
color of housing inclusive strain relief	black

lead

model	metal conduit 16 mm
inner cores	single cores LSOH
single cores	H07Z-R
color of the coding pin	white (C3)

model

nominal cross section conductor	2.5 mm²
degree of protection (IP)	IP20
wire strip length	10 mm
sheath strip length	200 mm
preparation of conductor ends	tin-plated
cable type	metal conduit 16 mm
version of cable	male - free end
type of cord set	connection cable
version cable end 1	free end
version cable end 2	MST20i3 plug

dimensions

total length	11 m