product data sheet

item no. G5.331.1306.1

cable assembly MST32I3KCB- 60 130BLC1

METALYNX² connection cable, female - free end, number of poles 3, rated voltage 250 V, rated current 32 A, cable type metal conduit 16 mm, fire class Eca, total length 13 m, nominal cross section conductor 6 mm², color of coding/ contact carrier blue

item no.	G5.331.1306.1
EAN	4049088246890
order unit	3 piece(s)

certificates / approvals

technical data

general

rated current	32 A
rated voltage	250 V
rated impulse voltage	4 kV
pollution degree	2
mechanical coding	code 1
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	blue
Pole codification	L, N, PE
color of housing inclusive strain relief	black

lead

model	metal conduit 16 mm
inner cores	single cores LSOH
single cores	H07Z-R
color of the coding pin	sky blue (C1)

model

nominal cross section conductor	6 mm²
degree of protection (IP)	IP20
wire strip length	10 mm
sheath strip length	800 mm
preparation of conductor ends	tin-plated
cable type	metal conduit 16 mm
version of cable	female - free end
type of cord set	connection cable
version cable end 1	MST32i3 female
version cable end 2	free end

dimensions

total length	13 m