product data sheet

item no. 92.051.5453.1

flat cable adapter GST18I5I B1H F7V SW

gesis® NRG flat cable adapter to GST18i5; Code 1 mains; colour of coding: black; 250/400 V; 20 A; pluggable output parallel to flat cable; piercing-contact screws with Torx-head; for gesis® NRG flatcable 5G2,5, 5G4, 5G2,5+2x1,5 und 5G4+2x1,5



item no.	92.051.5453.1
EAN	4049088287060
order unit	5 piece(s)

certificates / approvals

technical data

general

rated current	20 A
degree of protection (IP)	IP40
mechanical coding	code 1
Pole codification	3, N, PE, 2, 1
color of coding/ contact carrier	black
color housing	black
lockable	self-locking (unlocking by tool)

model

model	tapp-off

material

halogen free	yes
contact material	CuZn
fire load	0.589 kWh/St

dimensions


length	89.5 mm
width	61 mm
height	37.2 mm

accessories

item no.	type	description
05.564.5353.0	cover cap GST18I3/4/5 SW	Cover piece 12 pole black for female parts GST18i3-6
05.564.5353.2	cover cap GST18I3/4/5 WS	Cover piece 12 pole white for female parts GST18i3-6
05.566.9253.0	cover cap GST18I5 BUCHSEN	Cover for female connectors GST18i5, black
06.502.5810.0	screwdriver bit TX 10x25	Screw driver insert TX 10x25 for hexagon socket
06.502.6000.0	screwdriver TX10	Screw driver TX10 with insulated blade, grip printed with WIELAND logo

99.681.0000.0	sample case GESIS NRG 5x2,5+5x4MM²	gesis® NRG sample case 5G2,5 and 5G4 mmm²; contains feed-in and tapping gesis® NRG BASIC and DIMM, flat cable 5G2,5 mm² PVC pastel blue, flat cable 5G4 mm² halogenfree green, end caps, screw driver TX10.

technical drawing



Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit /E gekennzeichnete Maße sind nur für interne Zwecke gültig

These dimensions will be especially checked at delivery
Only inspection dimensions
With /E marked dimensions are only valid for internal use

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.

Tolerierung Size ISO 14405Ⓔ/Tolerance system Size ISO 14405Ⓔ.
(This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten.
Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach
General tolerance

CAD - Zeichnung, keine manuellen Änderungen
CAD - drawing, no manual modifications allowed

1.Verwendung: -
First Use:

Blatt: 1 von 1
Sheet: 1 of 1

	/		Werkstoff/Material	2015	Tag/Date	Name	Zeichnung Nr./Drawing No.	Index
	/		Farbe/colour:	gezeichnet drawn	21.1.	Ritter	92.051.5453.1 01K	a
	/	Maßstab/Scale	schwarz/black	geprüft checked	-	-		
	/	1:1		Normgepr. Stand. check	-	-	Maße in mm/Dimensions are in mm	
	/	Vol. mm³	Ofl./Surf. mm²	Ersatz für/Replacement for: -				
	/			Type	Benennung/Title			
a	13.05.2015/	wieland		GST18151	BUCHSENTEIL_5P			
Index	Datum / Blatt Date / Sheet	www.wieland-electric.com		B1H SW	female connector			
Änderung/Revision					für Flachbandleitung/ for flat conductor			