product data sheet

item no. 91.207.9900.2

cable assembly GST15I4KSBSX15 V 99WS

gesis® MINI connecting cable, female - male, in the 5 pole housing, number of poles 4, rated voltage 250 V / 400 V, rated current 16 A, cable type H05VV-F, fire class Eca, total length 10 m, nominal cross section conductor 1.5 mm², color of coding/ contact carrier white



item no.	91.207.9900.2
EAN	4049088329135
order unit	5 piece(s)

certificates / approvals

technical data

general

rated current	16 A
rated voltage	250 V / 400 V
rated impulse voltage	4 kV
pollution degree	2
mechanical coding	code 1
continuity resistor	114.9 mOhm
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	white
Pole codification	2, N, PE, 1
color of housing inclusive strain relief	white

model

nominal cross section conductor	1.5 mm²
degree of protection (IP)	IP20
cable type	H05VV-F
cable color	white
cable diameter max.	9.2 mm
version of cable	female - male, in the 5 pole housing
type of cord set	connecting cable
version cable end 1	GST15i4 socket
version cable end 2	GST15i4 plug

material

surface finish	silver-plated
halogen free	no
continuous temperature of cable	70 °C

insulation components continous temperature	100 °C
fire load	4.621 kWh/St
fire class	Eca

dimensions

total length	10 m