CSA INTERNATIONAL

Certificate of Compliance

Certificate: 1083359 (LR 62582-4)

Master Contract: 165750

Project: 1451758

Date Issued: June 30, 2003

Issued to: **Wieland Electrische Industrie GmbH**
Brennerstrasse 10-14
D-96052 BAMBERG/BAYERN
GERMANY

The products listed below are eligible to bear the CSA Mark shown

Authorized by: G. Foulem

PRODUCTS

CLASS 6233 01 - RECEPTACLES –Attachment Plug Type and Plugs

S-use connectors, Types 8113, 8213, 8313, 8413 rated 15 A, 300 V for all variations; except for tab connections Suffix SE rated 10 A; Suffix DFWW rated 6.5 A; Suffix DFLS rated 8 A; Suffix BSK rated 3 A for 20-18 AWG; Suffix BK rated 13 A for 14 AWG, 11 A for 16 AWG, 10 A for 18 AWG, 6 A for 20 AWG; Suffixes BFK, SUFK and for solder connections rated 12 A; 600 V for 8113/8213 BL.TR, B/3/2 through /23/12 and S/3/2 through /23/12; Suffix SU, rated 12 A, 300 V; Series 8813 rated 5 A, 300 V.

APPLICABLE REQUIREMENTS

CAN/CSA-C22.2 No. 0-M91	-	General Requirements
CSA Std C22.2 No 182.3-M1987	-	Special Use Attachment Plugs, Receptacles, and Connectors
CSA Std C22.2 No.158-1987	-	Terminal Blocks
TIL A-8A		