product data sheet

item no. 83.040.0711.0

IP switch WIENET SFP G MM FP



item no.	83.040.0711.0
EAN	4049088401626
order unit	1 piece(s)

certificates / approvals

technical data

operating temperature min.	-40 °C
operating temperature max.	85 °C
data rate (Mbps)	1250
wavelength (nm)	1310
light source	FP
media type	multi mode
Tx power (dBm)	-9...-1 @ 50/125 or 62,5/125 µm fiber
Rx sensitivity (dBm)	-19
linkbudget	10
saturation (dBm)	-1
distance	2000 m

accessories

item no.	type	description
F0.000.0053.8	accessories Router DIN RAIL CLIP LR/ER MET	