product data sheet

item no. 96.062.4153.6

# connector RST20I6S S1 ZR2 TB04

RST® CLASSIC connector, straight, number of poles 6, male, connection type screw connection, rated voltage 250 V / 400 V, rated current 16 A, cable diameter 10 - 14 mm, color of coding/ contact carrier turquoise blue



| | |
|---|---|
| item no. | 96.062.4153.6 |
| EAN | 4049088423598 |
| order unit | 100 piece(s) |

## certificates / approvals

## technical data

**note**

| | |
|---|---|
| note | wires with 2.5 mm² only without ferrules3 poles max. 20A, 3 poles max. 5A |

**general**

| | |
|---|---|
| rated current | 16 A |
| rated voltage | 250 V / 400 V |
| rated impulse voltage | 4 kV |
| strain relief | yes |
| pollution degree | 3 |
| lockable | self-locking (unlocking by tool) |
| color of coding/ contact carrier | turquoise blue |
| marking of poles | L, N, PE, 1, 2, Ls |
| color of housing inclusive strain relief | black |
| RAL-Nummer Codierung/Kontakteinsatz | 5018 |

**connection data**

| | |
|---|---|
| cable diameter max. | 14 mm |
| cable diameter min. | 10 mm |
| connection cross section solid mm² max. | 1.5 mm² |
| connection cross section solid mm² min. | 0.2 mm² |
| connection cross section fine stranded mm² max. | 1.5 mm² |
| connection cross section fine stranded mm² min. | 0.2 mm² |
| terminations per pole | 1 |
| sheath strip length | 25 mm |
| wire strip length | 8 mm |

**model**

| | |
|---|---|
| model | male |
| connection type | screw connection |
| degree of protection (IP) | IP66/68 (3m;2h) /IP69 |

**material**

| | |
|---|---|
| housing material | polyamide |
| halogen free | yes |
| contact material | CuZn |
| fire load | 0.318 kWh/St |
| insulation components continous temperature | 100 °C |
| surface finish | silver-plated |

**dimensions**

| | |
|---|---|
| length | 80 mm |
| width | 34.6 mm |
| height | 34.6 mm |

## accessories

| item no. | type | description |
|---|---|---|
| 99.591.0000.7 | cover for male connector SW | RST20i7/6 cover piece, for covering unused male connectors, with fastening belt, color black |
| Z5.569.5353.1 | cover for male connector SW | RST20i7/6 cover piece, for covering unused male connectors, color black |

## assembly


| item no. | type | description |
|---|---|---|
| 96.061.4153.6 | connector RST20I6S B1 ZR2 TB04 | RST® CLASSIC connector, straight, number of poles 6, female, connection type screw connection, rated voltage 250 V / 400 V, rated current 16 A, cable diameter 10 - 14 mm, color of coding/ contact carrier turquoise blue |
| 96.061.6053.6 | device connector RST20I6S B1 M00V TB04 | RST® CLASSIC device connector, modular, straight, M20, number of poles 6, model female, connection type screw connection, rated voltage 250 V / 400 V, rated current 20 A, color of coding/ contact carrier turquoise blue |
| 9L.061.6053.6 | device connector RST20I6S 11 M00V TB04 | RST® CLASSIC device connector, modular, straight, M20, number of poles 6, model female, connection type screw connection, rated voltage 250 V / 400 V, rated current 20 A, longitudinal sealing yes, color of coding/ contact carrier turquoise blue |
| 96.061.6153.6 | device connector RST20I6S B1 M03V TB04 | RST® CLASSIC device connector, modular, straight, M16, number of poles 6, model female, connection type screw connection, rated voltage 250 V / 400 V, rated current 20 A, color of coding/ contact carrier turquoise blue |
| 9L.061.6153.6 | device connector RST20I6S 11 M03V TB04 | RST® CLASSIC device connector, modular, straight, M16, number of poles 6, model female, connection type screw connection, rated voltage 250 V / 400 V, rated current 20 A, longitudinal sealing yes, color of coding/ contact carrier turquoise blue |
| 96.063.6053.6 | device connector RST20I6S B1 M90V TB04 | RST® CLASSIC device connector, modular, angled 90°, M20, number of poles 6, model female, connection type screw connection, rated voltage 250 V / 400 V, rated current 20 A, color of coding/ contact carrier turquoise blue |
| 96.063.6253.6 | device connector RST20I6S B1 M90V TB04 | RST® CLASSIC device connector, modular, angled 90°, M25, number of poles 6, model female, connection type screw connection, rated voltage 250 V / 400 V, rated current 20 A, color of coding/ contact carrier turquoise blue |
| 96.065.6153.6 | device connector RST20I6S B1 M13V TB04 | RST® CLASSIC device connector, modular, angled 7°, M16, number of poles 6, model female, connection type screw connection, rated voltage 250 V / 400 V, rated current 20 A, color of coding/ contact carrier turquoise blue |
| 96.061.6253.6 | device connector RST20I6S B1 M01V TB04 | RST® CLASSIC device connector, modular, straight, M25, number of poles 6, model female, connection type screw connection, rated voltage 250 V / 400 V, rated current 20 A, color of coding/ contact carrier turquoise blue |
| 9L.061.6253.6 | device connector RST20I6S 11 M01V TB04 | RST® CLASSIC device connector, modular, straight, M25, number of poles 6, model female, connection type screw connection, rated voltage 250 V / 400 V, rated current 20 A, longitudinal sealing yes, color of coding/ contact carrier turquoise blue |


technical drawing

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.


These dimensions will be especially checked at delivery
Only inspection dimensions
With /E marked dimensions are only valid for internal use


Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit /E gekennzeichnete Maße sind nur für interne Zwecke gültig






Auslieferungszustand
/delivery status





| Teile-Nr./ Part no. | Typ/ Type | Kodierung/ coding |
|---|---|---|
| 96.072.4153.0 | RST2017S S1 ZR2 GL |  |
| 96.072.4153.1 | RST2017S S1 ZR2 SW | |
| 96.072.4153.9 | RST2017S S1 ZR2 BL07 |  |
| 96.062.4153.6 | RST2016S S1 ZR2 TB04 |  |
| 96.072.4153.6 | RST2017S S1 ZR2 TB04 |  |

1:2



● = Pol verschlossen /pole closed

Tolerierung Size ISO 14405 Ⓔ / Tolerance system Size ISO 14405 Ⓔ.
(This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten. Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance

CAD - Zeichnung, keine manuellen Änderungen
CAD - drawing, no manual modifications allowed

1. Verwendung: First Use:

Blatt: 1 von 1
Sheet: 1 of 1

| | | | Tag/Date | Name |
|---|---|---|---|---|
| Werkstoff / Material | | gezeichnet drawn | 16.11.2017 | Hollet |
| Maßstab / Scale 1:1 | | geprüft checked | | |
| | | Normgeor. Stand. check | | |

Zeichnung Nr. / Drawing No. 96.072.4153.0 13K — Index a

Maße in mm / Dimensions are in mm

Vol. mm³ Oft./Srf. mm²

Ersatz für / Replacement for:

| Index | Datum / Blatt Date / Sheet | Änderung / Revision |
|---|---|---|
| a. | 14.05.2018 / | |

wieland
www.wieland-electric.com

Type RST20I

Bennenung/Title
ST_SCHRAUB
ohne Drahtschutz
male, screw connection without wire protection