product data sheet

item no. 96.040.0151.4

distributor RST20I4B 3P1 F VGB BR06

RST® CLASSIC distributor, parallel connection, with fastening option, number of poles 4, rated voltage 50 V / 120 V, rated current 20 A, number of inputs 1, number of outputs 3, color of coding/ contact carrier signal brown



item no.	96.040.0151.4
EAN	4049088347276
order unit	1 piece(s)

certificates / approvals

technical data

general

rated current	20 A
rated voltage	50 V / 120 V
rated impulse voltage	4 kV
pollution degree	3
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	signal brown
color of separate housing (only for modular versions)	black
marking of poles	1, 2, 3, 4

model

number of inputs	1
number of outputs	3
type of fastening	yes
degree of protection (IP)	IP66/68 (3m;2h) /IP69
type of distributor	compact distributor

material

housing material	polyamide
halogen free	yes
contact material	CuZn
fire load	1.966 kWh
insulation components continous temperature	100 °C
surface finish	silver-plated

dimensions

length	162 mm
width	104 mm
height	57.2 mm

accessories

item no.	type	description
05.565.9953.1	cover for male connector SW	RST20i5/4 cover piece, for covering unused male connectors, color black
99.530.0000.7	cover for female connector SW	RST20i5/4 cover piece, for covering unused female connectors, with fastening belt, color black

99.532.0000.7	cover for male connector SW	RST20i5/4 cover piece, for covering unused male connectors, with fastening belt, color black
Z5.565.9853.1	cover for female connector SW	RST20i5/4 cover piece, for covering unused female connectors, color black