product data sheet

item no. 75.452.0053.1

connecting module FCS 16 5 SI SA RST

podis® CON 5G16 connecting module, rated voltage 400 V, rated current 20 A, output RST20i5 Female, IP65, color housing black



item no.	75.452.0053.1
EAN	4049088476990
order unit	2 piece(s)

certificates / approvals

c UL us LISTED

technical data

note

note	through-current flat cable / power bus up to 63 A

connection data

number of poles	5
number of clamp positions per pole	1
type of termination (round cable)	insulation piercing connection
type of connection power bus	plug-in connection
number of outputs	1
output type	RST20i5 Female

technical data UL/CSA

rated voltage	600 V
rated current	20 A

mechanical data

housing material	polyamide
color housing	black
halogen free	yes
UV resistant	yes
shock resistance	IK10
degree of protection (IP)	IP65
mounting method	surface mounting

electrical data

rated voltage	400 V
rated current	20 A
type of supply voltage	AC

dimensions

length	218 mm
assembly width	84 mm
assembly height	80 mm

accessories

item no.	type	description
99.530.0000.7	cover for female connector SW	RST20i5/4 cover piece, for covering unused female connectors, with fastening belt, color black
Z5.565.9853.1	cover for female connector SW	RST20i5/4 cover piece, for covering unused female connectors, color black
06.502.6410.0	bit TX 15x70	Bit Torx TX 15x70