product data sheet

item no. 75.252.0053.1

connecting module FCS 6 5 SI SA RST20i5

podis® CON 5G6 connecting module, rated voltage 690 V, rated current 20 A, output RST20i5 Female, IP65, color housing black



item no.	75.252.0053.1
EAN	4049088461972
order unit	2 piece(s)

certificates / approvals

technical data

note

note	plug connection RST

connection data

number of poles	5
number of clamp positions per pole	1
type of termination (round cable)	insulation piercing connection
type of connection power bus	screw connection
number of outputs	1
output type	RST20i5 Female

technical data UL/CSA

rated voltage	600 V
rated current	20 A

mechanical data

color housing	black
degree of protection (IP)	IP65
mounting method	surface mounting

electrical data

rated voltage	690 V
rated current	20 A
type of supply voltage	AC

dimensions

length	218 mm
assembly width	84 mm
assembly height	74 mm

accessories

item no.	type	description
99.530.0000.7	cover for female connector SW	RST20i5/4 cover piece, for covering unused female connectors, with fastening belt, color black
Z5.565.9853.1	cover for female connector SW	RST20i5/4 cover piece, for covering unused female connectors, color black

06.502.6410.0	bit TX 15x70	Bit Torx TX 15x70