
product data sheet

item no. 56.202.8055.0

initiator terminal WTP 1,5 I/O-3

Initiator terminal with push in connection for mounting on TS 35,nominal cross section: 1,5 mm²,Width: 3,5 mm,Color: grey



item no.	56.202.8055.0
EAN	4049088432422
order unit	50 piece(s)

certificates / approvals

technical data

general

nominal cross section	1.5 mm²
color	grey
number of levels	2
width/grid dimension	3.5 mm
insulating housing	PA666
inflammability class of insulation material acc. with UL94	V0
Anschlussart	plug-in connection
Brennbarkeitsklasse des Isolierstoffs	V0

technical data

rated current	13.5 A
rated voltage	250 V
rated impulse voltage	4 kV
pollution degree	3
type of insulation material	thermoplastic
length	94 mm
width	3.5 mm
height	42 mm

connection data

connection type	plug-in connection
connection type 1	plug-in connection
connection type 2	plug-in connection
minimum cross section solid	0.14 mm²
maximum cross section solid	2.5 mm²
minimum cross section fine stranded	0.14 mm²
maximum cross section fine stranded	1.5 mm²
minumum conductor cross section (flex., stranded) with cable end sleeve	0.5 mm²

maximum conductor cross section (flex., stranded) with cable end sleeve	1.5 mm²
wire strip length	8 mm