
product data sheet

item no. 92.050.7353.0

distributor GST18I5V 3P1 B V BL01

gesis® CLASSIC H-distributor, rated voltage 50 V, rated current 6 A, number of poles 5, degree of protection (ip) IP40, number of inputs 1, number of outputs 3, pole codification 1, 2, 3, 4, 5, mechanical coding code 6, color of coding/ contact carrier light blue, ral number coding/contact insert 5012, halogen free yes, housing material polyamide, with fastening option to 07.413.6853.1/0, fire load 0.224 kWh/St, contact material CuZn, surface finish silver-plated, pollution degree 2, rated impulse voltage 4 kV, length 59 mm, height 40 mm, width 57.4 mm



item no.	92.050.7353.0
EAN	4049088350917
order unit	20 piece(s)

certificates / approvals

technical data

general

rated current	6 A
rated voltage	50 V
rated impulse voltage	4 kV
pollution degree	2
mechanical coding	code 6
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	light blue
Pole codification	1, 2, 3, 4, 5
RAL number coding/contact insert	5012

model

number of inputs	1
number of outputs	3
type of fastening	yes
degree of protection (IP)	IP40
type of distributor	H-distributor

material

housing material	polyamide
halogen free	yes
contact material	CuZn
fire load	0.224 kWh/St
insulation components continous temperature	100 °C
surface finish	silver-plated


dimensions


length	59 mm
width	57.4 mm
height	40 mm

accessories

item no.	type	description
07.413.6853.1	supporting plate GST18 VERTEILER SW	gesis®-Mounting plate for GST18-distributors. For fastening to load- bearing, straight surfaces; fixing on cable trays with moulded expanding rivets; lying distributor mounting; color black
05.564.5353.0	cover cap GST18I3/4/5 SW	Cover piece 12 pole black for female parts GST18i3-6
05.564.5353.2	cover cap GST18I3/4/5 WS	Cover piece 12 pole white for female parts GST18i3-6
05.566.9253.0	cover cap GST18I5 BUCHSEN	Cover for female connectors GST18i5, black

technical drawing





Teile-Nr./part-no.	Farbe/colour	Typ/type
92.050.7353.0	lichtblau/light blue	GST18I5V 3P1 B V BL01

Weitere Daten siehe KATALOG oder eKATALOG.
Additional data see CATALOG or eCATALOG.

www.wieland-electric.com
eshop.wieland-electric.com

Tolerierung Size ISO 14405 Ⓔ / Tolerance system Size ISO 14405 Ⓔ.
(This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020 010 ist einzuhalten. Conformity with Wieland document WN 5020 010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance

CAD - Zeichnung, keine manuellen Änderungen
CAD - drawing, no manual modifications allowed

1. Verwendung: First Use:

Blatt: 1 von
Sheet: 1 of

Werkstoff / Material

	Tag/Date	Name
gezeichnet drawn	16.06.2016	Ritter K.
geprüft checked		
Normgeor. Stand. check		

Zeichnung Nr. / Drawing No.: 92.050.7353.0 13K

Index

Maßstab / Scale: 1:1

Maße in mm / Dimensions are in mm

Vol.: --- mm³ Ofl./Surf.: --- mm²

Ersatz für / Replacement for:

Index | Datum / Blatt Date / Sheet | Änderung / Revision

wieland
www.wieland-electric.com

Type: GST18I5V

Bennenung/Title: VERTEILER_H

distributor

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße

Mit /E gekennzeichnete Maße sind nur für interne Zwecke gültig

These dimensions will be especially checked at delivery
Only inspection dimensions

With /E marked dimensions are only valid for internal use

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. The reproduct of distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.