
product data sheet

item no. 92.050.7153.0

distributor GST18I5V 3P1 B V TB05

gesis® CLASSIC H-distributor, with fastening option to 07.413.6853.1/0, number of poles 5, rated voltage 250 V / 400 V, rated current 13 A, number of inputs 1, number of outputs 3, color of coding/ contact carrier turquoise blue



item no.	92.050.7153.0
EAN	4049088350894
order unit	20 piece(s)

certificates / approvals

technical data

general

rated current	13 A
rated voltage	250 V / 400 V
rated impulse voltage	4 kV
pollution degree	2
mechanical coding	code 5
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	turquoise blue
Pole codification	1, 2, 3, 4/N, 5
RAL number coding/contact insert	5018

model

number of inputs	1
number of outputs	3
type of fastening	yes
degree of protection (IP)	IP40
type of distributor	H-distributor

material

housing material	polyamide
halogen free	yes
contact material	CuZn
fire load	0.223 kWh/St
insulation components continous temperature	100 °C
surface finish	silver-plated

dimensions

length	59 mm

width	57.4 mm
height	40 mm


accessories


item no.	type	description
07.413.6853.1	supporting plate GST18 VERTEILER SW	gesis®-Mounting plate for GST18-distributors. For fastening to load- bearing, straight surfaces; fixing on cable trays with moulded expanding rivets; lying distributor mounting; color black
05.588.5753.1	lock GST18 VERTEILER SW	Locking device for distributer GST18i3-5, retrofit part, black
05.564.5353.0	cover cap GST18I3/4/5 SW	Cover piece 12 pole black for female parts GST18i3-6
05.564.5353.2	cover cap GST18I3/4/5 WS	Cover piece 12 pole white for female parts GST18i3-6
05.566.9253.0	cover cap GST18I5 BUCHSEN	Cover for female connectors GST18i5, black
05.583.1853.0	cover cap GST18I5 STECKER	


technical drawing

These dimensions will be especially checked at delivery
Only inspection dimensions
With /E marked dimensions are only valid for internal use

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit /E gekennzeichnete Maße sind nur für interne Zwecke gültig







Teile-Nr./part-no.	Farbe/colour	Typ/type
92.050.7153.0	türkisblau/turquoise blue	GST18I5V 3P1 B V TB05

Weitere Daten siehe KATALOG oder eKATALOG.
Additional data see CATALOG or eCATALOG.

www.wieland-electric.com
eshop.wieland-electric.com

Tolerierung Size ISO 14405 Ⓔ / Tolerance system Size ISO 14405 Ⓔ.
(This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten. Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach
General tolerance

CAD - Zeichnung, keine manuellen Änderungen
CAD - drawing, no manual modifications allowed

1. Verwendung:
First Use:

Blatt: 1 von
Sheet: 1 of

Werkstoff / Material

	Tag/Date	Name
gezeichnet / drawn	16.06.2016	Ritter K.
geprüft / checked		
Normgeor. Stand: check		

Zeichnung Nr. / Drawing No.: 92.050.7153.0 13K

Index

Maßstab / Scale: 1:1

Maße in mm / Dimensions are in mm

Vol.. --- mm³ Ofl./Surf. --- mm²

Ersatz für / Replacement for:

Index | Datum / Blatt Date / Sheet

Änderung / Revision

wieland
www.wieland-electric.com

Type: GST18I5V

Bennenung/Title: VERTEILER_H

distributor

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.