
product data sheet

item no. 92.030.7553.0

distributor GST18I3V 3P1 B V RT03

gesis® CLASSIC H-distributor, with fastening option to 07.413.6853.1/0, number of poles 3, rated voltage 250 V, rated current 20 A, number of inputs 1, number of outputs 3, color of coding/ contact carrier salmon pink



item no.	92.030.7553.0
EAN	4049088350788
order unit	20 piece(s)

certificates / approvals

technical data

general

rated current	20 A
rated voltage	250 V
rated impulse voltage	4 kV
pollution degree	2
mechanical coding	code 3
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	salmon pink
Pole codification	L, N, PE
RAL number coding/contact insert	3022

model

number of inputs	1
number of outputs	3
type of fastening	yes
degree of protection (IP)	IP40
type of distributor	H-distributor

material

housing material	polyamide
halogen free	yes
contact material	CuZn
fire load	0.162 kWh/St
insulation components continous temperature	100 °C
surface finish	silver-plated

dimensions

length	59 mm
width	37.9 mm
height	40 mm


accessories


item no.	type	description
07.413.6853.1	supporting plate GST18 VERTEILER SW	gesis®-Mounting plate for GST18-distributors. For fastening to load- bearing, straight surfaces; fixing on cable trays with moulded expanding rivets; lying distributor mounting; color black
05.561.3653.0	cover cap GST18I3VS B WS	Cover piece for female GST18i3, white
05.561.3653.1	cover cap GST18I3VS B SW	Cover piece for female GST18i3, black
05.564.5353.0	cover cap GST18I3/4/5 SW	Cover piece 12 pole black for female parts GST18i3-6
05.564.5353.2	cover cap GST18I3/4/5 WS	Cover piece 12 pole white for female parts GST18i3-6
05.594.4250.0	cover cap ST18/3B + GST18I3 ST WS	
05.594.4253.0	cover cap ST18/3B + GST18I3 ST WS	


technical drawing

These dimensions will be especially checked at delivery
Only inspection dimensions
With /E marked dimensions are only valid for internal use

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit /E gekennzeichnete Maße sind nur für interne Zwecke gültig







Teile-Nr./part-no.	Farbe/colour	Typ/type
92.030.7553.0	lachsrot/salmon red	GST18I3V 3P1 B V RT03

Weitere Daten siehe KATALOG oder eKATALOG.
Additional data see CATALOG or eCATALOG.

www.wieland-electric.com
eshop.wieland-electric.com

Tolerierung Size ISO 14405 Ⓔ / Tolerance system Size ISO 14405 Ⓔ.
(This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020 010 ist einzuhalten.
Conformity with Wieland document WN 5020 010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach
General tolerance

CAD - Zeichnung, keine manuellen Änderungen
CAD - drawing, no manual modifications allowed

1. Verwendung:
First Use:

Blatt: 1 von
Sheet: 1 of

Werkstoff / Material

Maßstab / Scale: 1:1

	Tag/Date	Name
gezeichnet / drawn	15.06.2016	Ritter K.
geprüft / checked		
Normgeor. Stand. check		

Zeichnung Nr. / Drawing No.: 92.030.7553.0 13K

Index

Maße in mm / Dimensions are in mm

Vol.. --- mm³ Ofl./Surf. --- mm²

Ersatz für / Replacement for:

Index | Datum / Blatt Date / Sheet

Änderung / Revision

wieland
www.wieland-electric.com

Type: GST18I3V

Bennenung/Title: VERTEILER_H

distributor

Ritter_92_030_7553_013K-AA-dwg1_sheet_2 CADW3025 Ritter 2016-07-08T08:41:36 1.000

QU-MEE-01/14 a

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.