product data sheet

item no. 76.327.6428.0

bottom BAS GUT GW 24H A

Bottom-base revos basic made of aluminum, with single locking lever andprotective cover for terminal adapters mounted on the rear, open, high version, 24-poles

item no.	76.327.6428.0
EAN	4015573231009
order unit	1 piece(s)

certificates / approvals

technical data

general

housing material	aluminum
color	grey
surface	with powder coating
UV resistant	yes
inflammability class of insulation material acc. with UL94	other
operating temperature range min.	-40 °C
operating temperature range max.	120 °C

model

locking mechanism	single locking lever
thread size PG	
EMC-version	no