product data sheet

item no. 99.404.9999.7

surface mount socket RST20/25

RST20/25 surface mount socket



item no.	99.404.9999.7
EAN	4049088558931
order unit	5 piece(s)

certificates / approvals

technical data

technical data

length	81 mm
width	81 mm
height	43 mm
color	white
type of construction	surface mount socket

assembly

item no.	type	description
96.031.1053.1	device connector RST20I3F B2 M01 SW	RST® CLASSIC device connector, standard, straight, M25, number of poles 3, model female, connection type spring clamp connection, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier black
96.031.5053.1	device connector RST20I3S B1 M01 SW	RST® CLASSIC device connector, standard, straight, M25, number of poles 3, model female, connection type screw connection, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier black
99.405.9999.7	cable assembly RST20I3K1-KFX 15 30SW	RST® CLASSIC connecting cable, female - male, number of poles 3, rated voltage 250 V, rated current 16 A, cable type H07RN-F, fire class Eca, total length 3 m, nominal cross section conductor 1.5 mm², color of coding/ contact carrier black

technical drawing

