product data sheet

item no. 96.071.6253.6

# device connector RST20I7S B1 M01V TB04

RST® CLASSIC device connector, modular, straight, M25, number of poles 7, model female, connection type screw connection, rated voltage 250 V / 400 V, rated current 20 A, color of coding/ contact carrier turquoise blue



| | |
|---|---|
| item no. | 96.071.6253.6 |
| EAN | 4049088488115 |
| order unit | 100 piece(s) |

## certificates / approvals

## technical data

**note**

| | |
|---|---|
| note | 3 poles max. 20A, 4 poles max. 5Awires with 2.5 mm² only without ferrulespositioning realised with flattened thread |

**general**

| | |
|---|---|
| rated current | 20 A |
| rated voltage | 250 V / 400 V |
| pollution degree | 3 |
| rated impulse voltage | 4 kV |
| continuity resistor | 0.65 mOhm |
| lockable | self-locking (unlocking by tool) |
| color of coding/ contact carrier | turquoise blue |
| marking of poles | L, N, PE, 1, 2, 3, 4 |
| color of separate adapter (if present) | black |

**connection data**

| | |
|---|---|
| connection cross section solid mm² max. | 2.5 mm² |
| connection cross section solid mm² min. | 0.2 mm² |
| connection cross section fine stranded mm² max. | 2.5 mm² |
| connection cross section fine stranded mm² min. | 0.2 mm² |
| terminations per pole | 1 |
| wire strip length | 8 mm |

**model**

| | |
|---|---|
| model | female |
| connection type | screw connection |
| connecting thread metric | M25 |
| angle of plug | straight |
| degree of protection (IP) | IP66/68 (3m;2h) /IP69 |
| thickness of housings (electrical device) | 0.5 mm |

| | |
|---|---|
| thickness of housings (electrical device) | 8 mm |

**material**

| | |
|---|---|
| housing material | polyamide |
| halogen free | yes |
| contact material | CuZn |
| fire load | 0.254 kWh/St |
| insulation components continous temperature | 100 °C |
| surface finish | silver-plated |


**dimensions**

| | |
|---|---|
| length | 73 mm |
| width | 34.6 mm |
| height | 34.6 mm |


## accessories


| item no. | type | description |
|---|---|---|
| 06.562.8753.0 | manual disconnect RST20i7 BG | Manual disconnect for later installation of RST20i7/i6 connectors, color concrete gray |
| 99.589.0000.7 | cover for female connector SW | RST20i7/6 cover piece, for covering unused female connectors, with fastening belt, color black |
| Z5.569.5253.1 | cover for female connector SW | RST20i7/6 cover piece, for covering unused female connectors, color black |

technical drawing





Auslieferungszustand
/delivery status



| Teile-Nr./ Part no. | Typ/ Type | Kodierung/ coding |
|---|---|---|
| 96.071.6253.0 | RST20I7S B1 M01V GL |  |
| 96.071.6253.1 | RST20I7S B1 M01V SW | |
| 9L.071.6253.0 | RST20I7S 11 M01V GL | |
| 9L.071.6253.1 | RST20I7S 11 M01V SW | |
| 96.071.6253.9 | RST20I7S B1 M01V BL07 |  |
| 9L.071.6253.9 | RST20I7S 11 M01V BL07 | |
| 96.061.6253.6 | RST20I6S B1 M01V TB04 |  |
| 9L.061.6253.6 | RST20I6S 11 M01V TB04 | |
| 96.071.6253.6 | RST20I7S B1 M01V TB04 |  |
| 9L.071.6253.6 | RST20I7S 11 M01V TB04 | |

1:2



● = Pol verschlossen /pole closed

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit /E gekennzeichnete Maße sind nur für externe Zwecke gültig

These dimensions will be especially checked at delivery
Only inspection dimensions
With /E marked dimensions are only valid for internal use

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.

Tolerierung Size ISO 14405 Ⓔ / Tolerance system Size ISO 14405 Ⓔ.
(This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten. Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance

CAD - Zeichnung, keine manuellen Änderungen
CAD - drawing, no manual modifications allowed

1. Verwendung: First Use:

Blatt: 1 von 1 Sheet: 1 of 1

Werkstoff / Material

Maßstab / Scale: 1:1

Vol. mm³ Oft./Srf. mm²

| | Tag/Date | Name |
|---|---|---|
| gezeichnet drawn | 16.11.2017 | Hollet |
| geprüft checked | | |
| Normgeor. Stand. check | | |

Zeichnung Nr. / Drawing No.: 96.071.6253.0 13K

Index: a

Maße in mm / Dimensions are in mm

Ersatz für / Replacement for:

| Index | Datum / Blatt Date / Sheet | Änderung / Revision |
|---|---|---|
| a. | 14.05.2018 / | |

wieland
www.wieland-electric.com

Type: RST20I

Bennenung/Title:

# BU_SCHRAUB

ohne Drahtschutz

female, screw connection without wire protection