product data sheet

item no. 96.131.0155.7

connector RST20I3C B1 ZR2SH GN02

RST® CLASSIC connector, straight, number of poles 3, female, connection type crimp, rated voltage 250 V / 400 V, rated current 20 A, cable diameter 10 - 14 mm, color of coding/ contact carrier leaves green



item no.	96.131.0155.7
EAN	4049088501838
order unit	100 piece(s)

certificates / approvals

technical data

note

note	crimp contacts have to ordered separately (under fits with)

general

rated current	20 A
rated voltage	250 V / 400 V
rated impulse voltage	4 kV
strain relief	yes
pollution degree	3
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	leaves green
Pole codification	1, 2, PE
color of housing inclusive strain relief	black
RAL-Nummer Codierung/Kontakteinsatz	6002

connection data

cable diameter max.	14 mm
cable diameter min.	10 mm
connection cross section fine stranded mm² max.	4 mm²
connection cross section fine stranded mm² min.	0.75 mm²
terminations per pole	1
sheath strip length	37 mm
wire strip length	8 mm

model

model	female
connection type	crimp
degree of protection (IP)	IP66/68 (3m;2h) /IP69

material

housing material	polyamide

halogen free	yes
contact material	CuZn
fire load	0.287 kWh/St
insulation components continous temperature	100 °C
surface finish	silver-plated

dimensions

length	82 mm
width	34.6 mm
height	34.6 mm

accessories


item no.	type	description
99.414.6205.2	cover for female connector SW	RST20i3/2 cover piece, for covering unused female connectors, with fastening belt, color black
Z5.564.4553.1	cover for female connector SW	RST20i3/2 cover piece, for covering unused female connectors, color black
02.122.9000.0	female contact CRIMP RST20i2/i3 1,0QMM	RST20i3/2 crimp contact, female, 20A, for cross section 1.0 mm²/AWG17
02.122.9100.0	female contact CRIMP RST20i2/i3 1,5QMM	RST20i3/2 crimp contact, female, 20A, for cross section 1.5 mm²/AWG16
02.122.9200.0	female contact CRIMP RST20i2/i3 2,5QMM	RST20i3/2 crimp contact, female, 20A, for cross section 2.5 mm²/AWG14
02.122.9300.0	female contact CRIMP RST20i2/i3 4,0QMM	RST20i3/2 crimp contact, female, 20A, for cross section 4.0 mm²/AWG12

technical drawing


Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.


These dimensions will be especially checked at delivery
Only inspection dimensions
With /E marked dimensions are only valid for internal use

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit /E gekennzeichnete Maße sind nur für interne Zwecke gültig



Auslieferungszustand/delivery status





Verpackungseinheit: 100 Stück
packaging unit: per 100

96.131.0155.7	RST2013C B1 ZR2S H GN02	grün/green
Bestellnummer /order number	Typ /type	Farbe /colour

Weitere Daten siehe KATALOG oder eKATALOG.
Additional data see CATALOG or eCATALOG.

www.wieland-electric.com
eshop.wieland-electric.com

Tolerierung Size ISO 14405 Ⓔ / Tolerance system Size ISO 14405 Ⓔ.
(This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten. Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance

CAD - Zeichnung, keine manuellen Änderungen
CAD - drawing, no manual modifications allowed

1. Verwendung: First Use:

Blatt: 1 von 1 Sheet: 1 of 1

Werkstoff / Material

Maßstab / Scale: 1:1

Vol. mm³ Oft./Srf. mm²

	Tag/Date	Name
gezeichnet drawn	12.06.2018	Duetsch T .
geprüft checked		
Normgeor. Stand. check		

Zeichnung Nr. / Drawing No.: 96.131.0155.7 13K

Index

Maße in mm / Dimensions are in mm

Ersatz für / Replacement for:

Type: RST2013C

Bennenung/Title: BUCHSENTEIL + ZE
Crimpanschluß / crimpversion
400V

wieland
www.wieland-electric.com

Index | Datum / Blatt Date / Sheet | Änderung / Revision