product data sheet

item no. 99.988.0000.7

distributor box RST20I2V 7P1 FV L SW

RST® CLASSIC multi-distribution unit 1I / 7O, rated voltage 250 V, rated current 20 A, number of poles 2, degree of protection (ip) IP66/68 (3m 2h) /IP69, number of inputs 1, number of outputs 7, pole codification L, N, mechanical coding code 0, color of coding/ contact carrier black, ral number



item no.	99.988.0000.7
EAN	4049088193224
order unit	1 piece(s)

certificates / approvals

technical data

general

rated current	20 A
rated voltage	250 V
rated impulse voltage	4 kV
pollution degree	3
mechanical coding	code 0
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	black
color of separate housing (only for modular versions)	black
Pole codification	L, N
RAL number coding/contact insert	9005

model

number of inputs	1
number of outputs	7
type of fastening	yes
degree of protection (IP)	IP66/68 (3m;2h) /IP69
type of distributor	multi-distribution unit

material

housing material	polyamide
halogen free	yes
contact material	CuZn
fire load	2.912 kWh/St
insulation components continous temperature	100 °C
surface finish	silver-plated

dimensions

length	162 mm
width	104 mm
height	96 mm

accessories

item no.	type	description
05.564.4453.1	cover for male connector SW	RST20i3/2 cover piece, for covering unused male connectors, color black
99.414.6205.2	cover for female connector SW	RST20i3/2 cover piece, for covering unused female connectors, with fastening belt, color black
99.416.6205.2	cover for male connector SW	RST20i3/2 cover piece, for covering unused male connectors, with fastening belt, color black
Z5.564.4553.1	cover for female connector SW	RST20i3/2 cover piece, for covering unused female connectors, color black

assembly

item no.	type	description
96.222.1033.1	cable assembly RST20I2K1B-315 10SW	RST® CLASSIC connection cable, female - free end, number of poles 2, rated voltage 250 V, rated current 16 A, cable type H07RN-F, total length 1 m, nominal cross section conductor 1.5 mm², color of coding/ contact carrier black
96.222.1034.1	cable assembly RST20I2K1-S315 10SW	RST® CLASSIC connection cable, free end - male, number of poles 2, rated voltage 250 V, rated current 16 A, cable type H07RN-F, total length 1 m, nominal cross section conductor 1.5 mm², color of coding/ contact carrier black
96.021.4053.1	connector RST20I2S B13ZR1 SW	RST® CLASSIC connector, straight, number of poles 2, female, connection type screw connection, rated voltage 250 V, rated current 20 A, cable diameter 6 - 10 mm, color of coding/ contact carrier black
96.022.4053.1	connector RST20I2S S13ZR1 V SW	RST® CLASSIC connector, straight, number of poles 2, male, connection type screw connection, rated voltage 250 V, rated current 20 A, cable diameter 6 - 10 mm, color of coding/ contact carrier black