product data sheet

item no. 41.022.4041.4

device connector RST08i3/2S S1 M02HL SG

RST® MICRO device connector, standard, straight, M14, number of poles 2, model male, connection type screw connection, rated voltage 50 V / 120 V, rated current 8 A, color of coding/ contact carrier slate grey



item no.	41.022.4041.4
EAN	4049088482311
order unit	50 piece(s)

certificates / approvals

technical data

note

note	RST® terminals with screw clamping allow the connection of conductors without special preparation (without ferrules) according to EN 60999-1.positioning realised with flattened thread

general

rated current	8 A
rated voltage	50 V / 120 V
pollution degree	3
rated impulse voltage	2.5 kV
continuity resistor	0.55 mOhm
lockable	self-locking (unlocking by hand)
color of coding/ contact carrier	slate grey
marking of poles	1, 2

connection data

connection cross section solid mm² max.	1 mm²
connection cross section solid mm² min.	0.2 mm²
connection cross section fine stranded mm² max.	1 mm²
connection cross section fine stranded mm² min.	0.22 mm²
terminations per pole	1
wire strip length	6 mm

model

model	male
connection type	screw connection
connecting thread metric	M14
angle of plug	straight
degree of protection (IP)	IP66/68 (3m;2h) /IP69

thickness of housings (electrical device)	0.5 mm
thickness of housings (electrical device)	4 mm

material

housing material	polyamide
halogen free	yes
contact material	CuZn
fire load	0 kWh/St
insulation components continous temperature	100 °C
surface finish	silver-plated

dimensions


length	21.3 mm
width	19.2 mm
height	19.2 mm

accessories


item no.	type	description
06.563.5153.1	cover for male connector SW	RST08i3/2 cover piece, for covering unused male connectors, with fastening belt, color black
06.502.6100.0	allen key RST MICRO SW 0,9	Allen Key for screw terminals RST® MICRO
06.502.6300.0	screwdriver RST MICRO SW 0,9	Screwdriver (hexagonal wrench 0.9) for RST® MICRO


technical drawing

Gezeichnete Ausführung/drawn version
41.032.4053.1



Auslieferungszustand/
delivery condition






Teile-Nr. / part-no.	Type	Kodierung / coding
41.032.4053.1	RST08i3 S S1 M02H SW	C1
4L.032.4053.1	RST08i3 S 21 M02H SW	
41.032.4043.9	RST08i3 S S1 M02H BL	C2
4L.032.4043.9	RST08i3 S 21 M02H BL	
41.032.4041.4	RST08i3 S S1 M02HL SG	C3
4L.032.4041.4	RST08i3 S 21 M02HL SG	
41.032.4051.8	RST08i3 S S1 M02HL KG	C4
4L.032.4051.8	RST08i3 S 21 M02HL KG	
41.022.4043.1	RST08i3/2S S1 M02H SW	C1
4L.022.4043.1	RST08i3/2S 21 M02H SW	
41.022.4043.9	RST08i3/2S S1 M02H BL	C2
4L.022.4043.9	RST08i3/2S 21 M02H BL	
41.022.4041.4	RST08i3/2S S1 M02HL SG	C3
4L.022.4041.4	RST08i3/2S 21 M02HL SG	
41.022.4041.8	RST08i3/2S S1 M02HL KG	C4
4L.022.4041.8	RST08i3/2S 21 M02HL KG	

●=Pol nicht bestückt
/pole not mounted

Gehäuseausschnitt
/cut out:



Weitere Daten siehe KATALOG oder eKatalog | www.wieland-electric.com
additional data see CATALOG or eCATALOG | eshop.wieland-electric.com

Tolerierung Size ISO 14405 Ⓔ / Tolerance system Size ISO 14405 Ⓔ.
(This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten. / conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach / General tolerance

CAD - Zeichnung, keine manuellen Änderungen / CAD - drawing, no manual modifications allowed

1. Verwendung: / First Use:

Blatt: 1 von 1 / Sheet: 1 of 1

Werkstoff / Material

Maßstab / Scale: 1:1

Vol. mm³ Oft./Srf. mm²

	Tag/Date	Name
gezeichnet / drawn	22.02.2018	Hollet
geprüft / checked		
Normgepr. Stand. check		

Zeichnung Nr. / Drawing No.: 41.032.4053.1 13K

Index

Maße in mm / Dimensions are in mm

Ersatz für / Replacement for:

Index	Datum / Blatt / Date / Sheet	Änderung / Revision
a	12.03.2020 /	

wieland
www.wieland-electric.com

Type: RSTmicro

Bennenung/Title: STECKERTEIL_GA
male device connector

Diese Maße werden bei Abnahme besonders geprüft / Ausschließlich Prüfmaße

Mit Ⓔ gekennzeichnete Maße sind nur für interne Zwecke gültig

These dimensions will be especially checked at delivery / Only inspection dimensions

With Ⓔ marked dimensions are only valid for internal use

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.