

product data sheet

item no. 46.433.1030.9

cable assembly RST16I3KSBS 25G 10BL07

RST® MINI connecting cable, female - male, number of poles 3, rated voltage 250 V, rated current 16 A, cable type H07RN-F, total length 1 m, nominal cross section conductor 2.5 mm², color of coding/ contact carrier light blue



item no.	46.433.1030.9
EAN	4049088603693
order unit	50 piece(s)

certificates / approvals



technical data

note

note	The total length may vary up to + / - 3 %.
------	--

general

rated current	16 A
rated voltage	250 V
rated impulse voltage	4 kV
pollution degree	3
continuity resistor	8.34 mOhm
lockable	self-locking (unlocking by hand)
color of coding/ contact carrier	light blue
Pole codification	1, 2, 3
color of housing inclusive strain relief	black

model

type of construction	cable screw gland
connection type	screw connection
nominal cross section conductor	2.5 mm²
degree of protection (IP)	IP66/68 (3m;2h) /IP69
cable type	H07RN-F
cable color	black
cable diameter min.	11.3 mm
cable diameter max.	11.9 mm
version of cable	female - male
type of cord set	connecting cable
version cable end 1	female
version cable end 2	male

material

surface finish	silver-plated
halogen free	no
insulation components continous temperature	100 °C
fire load	0 kWh/St

dimensions

total length	1 m
--------------	-----

