



UKCA-Declaration of Conformity

Product name: Configurable samos®PRO

Type designation: SP-COP1-A/-C; SP-COP1-P-A/-C; SP-COP1-M-A/-C
SP-COP2-EN-A/-C; SP-COP2-EN-P-A/-C
SP-COP2-ENI-A/-C; SP-COP2-ENI-P-A/-C; SP-COP2-ENI-M-A/-C
SP-SDIO84-P1-K-A/-C
SP-SDI8-P1-K-A/-C
SP-SAR4-A/-C; SP-SAC4-A/-C; SP-SACR22-A/-C
SP-DIO84-P1-K-A/-C
SA-OR-S1-4RK-A/-C; SA-OR-S2-2RK-A/-C
SP-PROFIBUS-DP
SP-CANopen; SP-EN-ETC
SP-COP-CARD1

Applicant: Wieland Electric GmbH,
Brennerstraße 10-14, 96052 Bamberg, Germany

complies with the following statutory requirements and carries the UKCA marking accordingly:

Regulation	Standard	Edition	relevant
SI 2008/1597 (MD)	EN ISO 13849-1	2023	
	EN ISO 13849-2	2012	
SI 2016/1091 (EMC)	EN 61131-2	2007	Clauses 6.1- 6.3, 8
SI 2012/3032 (RoHS)	EN IEC 63000	2018	
	EN 60664-1	2007	
	EN IEC 60664-1	2020 +AC:2020	
	IEC 61508 P. 1 - 7	2010	
	EN 61131-6	2012	
	EN 50156-2	2015	

Authorized documentation representative
Wieland Electric GmbH, Brennerstr. 10-14, 96052 Bamberg

Bamberg, den 12.06.2024

i. V. 

Marco Ludvik
Head of Electronic Development

Wieland Electric GmbH

i. V. 

Klaus Jungstädt
Head of Approval and Standards

Attachment to CE-Declaration of Conformity

Artikelnummer / Article No.	Typenbezeichnung / Type Designation	Seriennummernbereich / Range of serial numbers
R1.190.1110.0	SP-COP1-A	R11901110015010000 - R11901110029219999
R1.190.1120.0	SP-COP1-C	R11901120015010000 - R11901120029219999
R1.190.1130.0	SP-COP1-P-A	R11901130015010000 - R11901130029219999
R1.190.1140.0	SP-COP1-P-C	R11901140015010000 - R11901140029219999
R1.190.1210.0	SP-COP2-EN-A	R11901210015010000 - R11901210029219999
R1.190.1220.0	SP-COP2-EN-C	R11901220015010000 - R11901220029219999
R1.190.1230.0	SP-COP2-EN-P-A	R11901230015010000 - R11901230029219999
R1.190.1240.0	SP-COP2-EN-P-C	R11901240015010000 - R11901240029219999
R1.190.1310.0	SP-COP2-ENI-A	R11901310015010000 - R11901310029219999
R1.190.1320.0	SP-COP2-ENI-C	R11901320015010000 - R11901320029219999
R1.190.1330.0	SP-COP2-ENI-P-A	R11901330015010000 - R11901330029219999
R1.190.1340.0	SP-COP2-ENI-P-C	R11901340015010000 - R11901340029219999
R1.190.0030.0	SP-SDIO84-P1-K-A	R11900030015010000 - R11900030029219999
R1.190.0040.0	SP-SDIO84-P1-K -C	R11900040015010000 - R11900040029219999
R1.190.1050.0	SP-SDIO84-K-A	R11901050015010000 - R11901050029219999
R1.190.1060.0	SP-SDIO84-K-C	R11901060015010000 - R11901060029219999
R1.190.0050.0	SP-SDI8-P1-K-A	R11900050015010000 - R11900050029219999
R1.190.0060.0	SP-SDI8-P1-K -C	R11900060015010000 - R11900060029219999
R1.190.1610.0	SP-SAR4-A	R11901610019300000 - R11901610029219999
R1.190.1620.0	SP-SAR4-C	R11901620019300000 - R11901620029219999
R1.190.1630.0	SP-SAC4-A	R11901630019300000 - R11901630029219999
R1.190.1640.0	SP-SAC4-C	R11901640019300000 - R11901640029219999
R1.190.1650.0	SP-SACR22-A	R11901650019300000 - R11901650029219999
R1.190.1660.0	SP-SACR22-C	R11901660019300000 - R11901660029219999
R1.190.1150.0	SP-COP1-M-A	R11901150021010000 - R11901150029219999
R1.190.1160.0	SP-COP1-M-C	R11901160021010000 - R11901160029219999

R1.190.1250.0	SP-COP2-EN-M-A	R11901250021010000 - R11901250029219999
R1.190.1260.0	SP-COP2-EN-M-C	R11901260021010000 - R11901260029219999
R1.190.1350.0	SP-COP2-ENI-M-A	R11901350021010000 - R11901350029219999
R1.190.1360.0	SP-COP2-ENI-M-C	R11901360021010000 - R11901360029219999
R1.190.0190.1	SP-PROFIBUS-DP	
R1.190.0210.1	SP-CANopen	
R1.190.0160.0	SP-EN-ETC	
R1.180.0080.0	SA-OR-S1-4RK-A	
R1.180.0320.0	SA-OR-S2-2RK-A	
R1.180.0430.0	SA-OR-S1-4RK-C	
R1.180.0440.0	SA-OR-S2-2RK-C	
R1.190.1000.0	SP-COP-CARD1	