

Certificate of Compliance

Certificate: 1594191

Master Contract: 165750 (LR 62582)

Project: 80144964

Date Issued: 2022-12-19

Issued To: Wieland Electric GmbH
Brennerstrasse 10-14
Bamberg, Bavaria, 96052
Germany

Attention: Eshwar Kashyap

The products listed below are eligible to bear the CSA Mark shown



Michael Chung
Issued by: Michael Chung

PRODUCTS

CLASS 6233 01 - RECEPTACLES - Attachment Plug Type and Plugs

Special-use Connectors Series GST18I:

- Screw clamp Type (rewireable), torque 0.5-0.7 Nm, rated 20A max (Nos 12 to 22AWG, 400Vac (Interrupting), 600V (Non-interrupting),
- Crimp Type (rewireable), rated 20A max (Nos 12 to 22AWG), 400Vac (Interrupting), 600V (Non-interrupting).
- Snap-in chassis mount, screw clamp Type, rated 20A max (Nos 12 to 22AWG), 400Vac (Interrupting), 600V (Non-interrupting).
- Coupler and distribution block Type, rated 20A max, 400Vac (Interrupting), 600V (Non-interrupting).
- PCB mount Type, rated 20A max, 400Vac (Interrupting), 600V (Non-interrupting).

Note: Series GST18I3-5, single connectors series with a single-screw termination type alone, (rewireable and chassis mounting screw versions) may be used with (2) No 14 AWG stranded wires or (2) No 14 AWG consisting of (1) stranded and (1) solid wire in the ground contact, for a specific end use application.

Notes:

Products certified under Class C623301 have been certified under CSA's ISO/IEC 17065 accreditation with the Standards Council of Canada (SCC). www.scc.ca

