

product data sheet

item no. 75.256.0353.1

connection module double output FCS 6 5 SI SA
M32XF

podis® CON 5G16 connection module double output, rated voltage 690 V, rated current 41 A, cross section fine-stranded 1.5 mm² - 16 mm², output for M32 cable gland, IP65, color housing black



item no.	75.256.0353.1
EAN	4049088651946
order unit	1 piece(s)

certificates / approvals

technical data

connection data

number of poles	5
number of clamp positions per pole	1
type of termination (round cable)	insulation piercing connection
type of connection power bus	screw connection
number of outputs	2
output type	for M32 cable gland
cross section fine-stranded	1,5 mm² - 16 mm²
connection cross section solid	1,5 mm² - 16 mm²

mechanical data

color housing	black
degree of protection (IP)	IP65
mounting method	surface mounting

electrical data

rated voltage	690 V
rated current	41 A
type of supply voltage	AC

dimensions

length	219 mm
assembly width	84 mm
assembly height	140 mm

accessories

item no.	type	description
05.505.0253.1	Locknut M25 x 1,5	Locknut M25 x 1.5 in color black, polyamide
05.506.7353.1	locking screw M25x1,5	Locking screw made of plastic, thread: M25, color: black, locknut 05.505.0253.1 seperatly
Z5.507.1453.1	cable screw gland M25 x 1,5 9 - 16	Cable Gland M25 x 1.5 for cable diameters 9 - 16 mm, black, polyamide, Locknut 05.505.0253.1 separately

Z5.507.1553.1	cable screw gland M25 x 1,5 13 - 18	Cable Gland M25 x 1.5 for cable diameters 11 - 17 mm, black, polyamide, Locknut 05.505.0253.1 separately
---------------	-------------------------------------	---

