

product data sheet

item no. 75.456.0053.3

connecting module FCS 16 5 SI SA M32 LG

podis® CON 5G16 connecting module, rated voltage 690 V, rated current 63 A, cross section fine-stranded 1.5 mm² - 16 mm², output for M32 cable gland, IP65, color housing light grey



item no.	75.456.0053.3
EAN	4049088702846
order unit	2 piece(s)

certificates / approvals

technical data

connection data

number of poles	5
number of clamp positions per pole	1
type of termination (round cable)	insulation piercing connection
type of connection power bus	screw connection
number of outputs	1
output type	for M32 cable gland
cross section fine-stranded	1,5 mm² - 16 mm²

mechanical data

housing material	polyamide
color housing	light grey
halogen free	yes
degree of protection (IP)	IP65
mounting method	surface mounting

electrical data

rated voltage	690 V
rated current	63 A
type of supply voltage	AC

dimensions

length	248 mm
assembly width	84 mm
assembly height	80 mm

assembly

item no.	type	description
00.771.0307.3	flat cable FL-LSHF 5G16	podis® CON 5G16 flat cable FL-LSHF 5G16, number of cores 5, 16 mm², fire class B2ca s1 d1 a1, halogen free, color outer sheath grey.