


product data sheet

item no. 0D.S07.3427.0

insert bridge IVB WTN 6-4 IN

insert bridge IVB WTN 6-4 IN modular spacing 8 mm, insulated yes, number of poles 4, color grey, height 24.2 mm, mounting method screwable, inflammability class of insulation material acc. with UL94 V0



item no.	0D.S07.3427.0
EAN	4049088723469
order unit	200 piece(s)

certificates / approvals

technical data

general

color	grey
inflammability class of insulation material acc. with UL94	V0
width/grid dimension	30.5 mm
length	3.2 mm
modular spacing	8 mm
number of bridged clamps	4
mounting method	screwable
insulated	yes
model	cross connector
height	24.2 mm

