


product data sheet

item no. 0D.200.0355.0

end bracket WEFN 4N

end bracket WEFN 4N length 50 mm, height 35 mm, mounting method DIN rail (top hat rail), color grey, inflammability class of insulation material acc. with ul94 V0, terminal blocks for electrical installations yes



item no.	0D.200.0355.0
EAN	4049088717925
order unit	50 piece(s)

certificates / approvals

technical data

general

color	grey
inflammability class of insulation material acc. with UL94	V0
width/grid dimension	8 mm
latching	screwable
length	50 mm
mounting method	DIN rail (top hat rail)
height	35 mm
tightening moment	0.6 Nm
Reihenklappen für Installationsverteiler	yes
halogen free	yes

accessories

item no.	type	description
0D.202.7281.0	marking strips WML 9.8/60	marking strips WML 9.8/60 material plastic, color white, length 230 mm, height 15.1 mm, inflammability class of insulation material acc. with ul94 V0
0D.206.7056.0	marking plate WMP 8-10	marking plate WMP 8-10 modular spacing 8 mm, material plastic, color white, length 128 mm, height 76 mm, mounting method snap-on, inflammability class of insulation material acc. with ul94 V0

