

product data sheet

item no. 05.544.3229.8

male contact D 3,6- 6,0 QMM AG

Male contact, turned Ø 3,6 mm, 6 mm², AWG 10, Ag



item no.	05.544.3229.8
EAN	4015573450448
order unit	100 piece(s)

certificates / approvals

technical data

general

wire strip length	10 mm
min. conductor cross section flexible wire	6 mm ²
max. conductor cross section flexible wire	6 mm ²
min. UL/CSA wire diameter flexible wire	10 AWG
max. UL/CSA wire diameter flexible wire	10 AWG
connection type	crimp
material	other
massive contact	yes
contact pin diameter	3.6 mm
flammability class of insulation material acc. with UL94	other
contact resistance	≤ 1 mOhm

