

product data sheet

item no. 05.544.4129.8

male contact D 1,6- 0,14-0,37 QMM

Male contact, turned Ø 1,6 mm, 0,14-0,37 mm², AWG 26-22, Ag



item no.	05.544.4129.8
EAN	4015573450530
order unit	100 piece(s)

certificates / approvals



technical data

general

wire strip length	8 mm
min. conductor cross section flexible wire	0.14 mm ²
max. conductor cross section flexible wire	0.37 mm ²
min. UL/CSA wire diameter flexible wire	26 AWG
max. UL/CSA wire diameter flexible wire	22 AWG
connection type	crimp
material	brass
massive contact	yes
contact pin diameter	1.6 mm
flammability class of insulation material acc. with UL94	other
contact resistance	≤ 5 mOhm

accessories

item no.	type	description
05.502.2100.0	crimping die B	Crimp dies for revos crimping tool, usable for crimp-contacts with a cross section of 0.14-1.0 mm ² , 1.5 mm ² , 2.5 mm ² and 4.0 mm ²
05.502.3100.0	contact positioner 1	Contact positioner for crimp-contacts with a diameter of 1.6 mm, 2.5 mm and 3.6 mm
95.101.0800.0	basic crimping tool .	Crimping tool kit
05.502.0710.0	extraction tool MOD. 10POL.	Extraction tool for 10 pole revos FLEX module

