

product data sheet

item no. 02.125.4029.8

female contact D 2,5- 4,0 QMM AG

Female contact, turned Ø 2,5 mm, 4 mm<sup>2</sup>, AWG 12, Ag



|            |               |
|------------|---------------|
| item no.   | 02.125.4029.8 |
| EAN        | 4015573450677 |
| order unit | 100 piece(s)  |

certificates / approvals

technical data

**general**

|                                                          |                   |
|----------------------------------------------------------|-------------------|
| wire strip length                                        | 8 mm              |
| min. conductor cross section flexible wire               | 4 mm <sup>2</sup> |
| max. conductor cross section flexible wire               | 4 mm <sup>2</sup> |
| min. UL/CSA wire diameter flexible wire                  | 12 AWG            |
| max. UL/CSA wire diameter flexible wire                  | 12 AWG            |
| connection type                                          | crimp             |
| material                                                 | other             |
| massive contact                                          | yes               |
| contact pin diameter                                     | 2.5 mm            |
| flammability class of insulation material acc. with UL94 | other             |
| contact resistance                                       | ≤ 2 mOhm          |

