

product data sheet

item no. 02.125.3629.8

female contact D 2,5- 0,5 QMM AG

Female contact, turned Ø 2,5 mm, 0,5 mm², AWG 20, Ag




item no.	02.125.3629.8
EAN	4015573450639
order unit	100 piece(s)

certificates / approvals

technical data

general

wire strip length	8 mm
min. conductor cross section flexible wire	0.5 mm ²
max. conductor cross section flexible wire	0.5 mm ²
min. UL/CSA wire diameter flexible wire	20 AWG
max. UL/CSA wire diameter flexible wire	20 AWG
connection type	crimp
material	other
massive contact	yes
contact pin diameter	2.5 mm
flammability class of insulation material acc. with UL94	other
contact resistance	≤ 2 mOhm



2021253629801K	4 CADW1016 Hoffman	2008-01-25T15:04:11	1 000
----------------	--------------------	---------------------	-------