


product data sheet

item no. 02.125.3529.8

female contact D 2,5- 1,5-2,5 QMM

Female contact, stamped Ø 2,5 mm, 1,5-2,5 mm², AWG 16-14, Ag



item no.	02.125.3529.8
EAN	4015573450622
order unit	100 piece(s)

certificates / approvals

technical data

general

wire strip length	4 mm
min. conductor cross section flexible wire	1.5 mm ²
max. conductor cross section flexible wire	2.5 mm ²
min. UL/CSA wire diameter flexible wire	16 AWG
max. UL/CSA wire diameter flexible wire	14 AWG
connection type	crimp
material	bronze
massive contact	no
contact pin diameter	2.5 mm
flammability class of insulation material acc. with UL94	other
contact resistance	≤ 5 mOhm