

product data sheet

item no. 05.543.7402.0

male contact 4 QMM AG



item no.	05.543.7402.0
EAN	4015573083110
order unit	200 piece(s)

certificates / approvals

technical data

general

wire strip length	7 mm
min. conductor cross section flexible wire	4 mm ²
max. conductor cross section flexible wire	4 mm ²
min. UL/CSA wire diameter flexible wire	12 AWG
max. UL/CSA wire diameter flexible wire	12 AWG
connection type	crimp
material	brass
massive contact	yes
contact pin diameter	2.5 mm
flammability class of insulation material acc. with UL94	other
contact resistance	≤ 1.5 mOhm

