


# product data sheet

item no. 25.330.3953.0

## PCB pin header 8113 S / 9 G OB

PCB pin header, connection method depends on used socket part ,  
9 poles, pitch: 5 mm, type of packing: carton, color: grey



|            |               |
|------------|---------------|
| item no.   | 25.330.3953.0 |
| EAN        | 4015573185210 |
| order unit | 50 piece(s)   |

### certificates / approvals



### technical data

#### general

|                                          |                |
|------------------------------------------|----------------|
| modular spacing                          | 5 mm           |
| soldering process                        | wave soldering |
| packaging                                | carton         |
| number of poles                          | 9              |
| number of levels                         | 1              |
| marking                                  | no             |
| fastening                                | none           |
| mating direction towards (circuit) board | 90°            |

#### technical data

|                          |        |
|--------------------------|--------|
| rated current            | 12 A   |
| overvoltage category I   | 1000 V |
| overvoltage category II  | 400 V  |
| overvoltage category III | 250 V  |
| rated impulse voltage    | 4 kV   |

#### technical data UL/CSA

|                        |       |
|------------------------|-------|
| voltage UL             | 300 V |
| current field wiring   | 15 A  |
| current factory wiring | 15 A  |
| voltage CSA            | 300 V |
| current CSA            | 15 A  |

#### other

|                             |               |
|-----------------------------|---------------|
| type of insulation material | thermoplastic |
| color                       | grey          |

|                          |         |
|--------------------------|---------|
| height                   | 12 mm   |
| length                   | 46.4 mm |
| depth                    | 8.4 mm  |
| material contact base    | CuZn    |
| material contact surface | Sn      |

#### assembly

| item no.      | type                              | description                                                                                                                                                                                     |
|---------------|-----------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 25.220.3953.0 | PCB connector 8113 B / 9 TOP OB   | PCB female connector with front/top screw connection, 9 poles, max. cross section: 2.5 mm <sup>2</sup> , pitch: 5 mm, type of packing: carton, color: grey                                      |
| 25.220.0953.0 | PCB connector 8113 B / 9 TOP      | PCB female connector with front/top screw connection, 9 poles, printed version, max. cross section: 2.5 mm <sup>2</sup> , pitch: 5 mm, type of packing: carton, color: grey                     |
| 01.060.3953.0 | PCB connector 8113 BK / 9 OB      | PCB female connector with Crimp connection, 9 poles, max. cross section: 2.5 mm <sup>2</sup> , pitch: 5 mm, type of packing: carton, color: grey                                                |
| 01.060.0953.0 | PCB connector 8113 BK / 9         | PCB female connector with Crimp connection, 9 poles, printed version, max. cross section: 2.5 mm <sup>2</sup> , pitch: 5 mm, type of packing: carton, color: grey                               |
| 25.320.3953.0 | PCB connector 8113 B / 9 OB       | PCB female connector with screw connection with rising cage clamp system, 9 poles, max. cross section: 2.5 mm <sup>2</sup> , pitch: 5 mm, type of packing: carton, color: grey                  |
| 25.320.0953.0 | PCB connector 8113 B / 9          | PCB female connector with screw connection with rising cage clamp system, 9 poles, printed version, max. cross section: 2.5 mm <sup>2</sup> , pitch: 5 mm, type of packing: carton, color: grey |
| 25.325.3953.0 | PCB connector 8113 B / 9 VR OB    | PCB female connector with screw connection with rising cage clamp system, 9 poles, max. cross section: 2.5 mm <sup>2</sup> , pitch: 5 mm, type of packing: carton, color: grey                  |
| 25.325.0953.0 | PCB connector 8113 B / 9 VR       | PCB female connector with screw connection with rising cage clamp system, 9 poles, printed version, max. cross section: 2.5 mm <sup>2</sup> , pitch: 5 mm, type of packing: carton, color: grey |
| 25.326.3953.0 | PCB connector 8113 B / 9 VL OB    | PCB female connector with screw connection with rising cage clamp system, 9 poles, max. cross section: 2.5 mm <sup>2</sup> , pitch: 5 mm, type of packing: carton, color: grey                  |
| 25.326.0953.0 | PCB connector 8113 B / 9 VL       | PCB female connector with screw connection with rising cage clamp system, 9 poles, printed version, max. cross section: 2.5 mm <sup>2</sup> , pitch: 5 mm, type of packing: carton, color: grey |
| 25.820.3953.0 | PCB connector 8113 BFK / 9 TOP OB | PCB female connector with tension spring connection, 9 poles, max. cross section: 2.5 mm <sup>2</sup> , pitch: 5 mm, type of packing: carton, color: grey                                       |
| 25.820.0953.0 | PCB connector 8113 BFK / 9 TOP    | PCB female connector with tension spring connection, 9 poles, printed version, max. cross section: 2.5 mm <sup>2</sup> , pitch: 5 mm, type of packing: carton, color: grey                      |

