

product data sheet

item no. 96.031.6153.0

device connector RST20I3S B1 M03 GL

RST® CLASSIC device connector, modular, straight, M16, number of poles 3, model female, connection type screw connection, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier light grey



item no.	96.031.6153.0
EAN	4015573904866
order unit	100 piece(s)

certificates / approvals



technical data

note

note	RST® terminals with screw clamping allow the connection of conductors without special preparation (without ferrules) according to EN 60999-1. positioning realised with flattened thread
------	--

general

rated current	20 A
rated voltage	250 V
pollution degree	3
rated impulse voltage	4 kV
continuity resistor	0.55 mOhm
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	light grey
marking of poles	L, N, PE
color of separate adapter (if present)	light grey

connection data

connection cross section solid mm² max.	6 mm²
connection cross section solid mm² min.	0.75 mm²
connection cross section fine stranded mm² max.	6 mm²
connection cross section fine stranded mm² min.	0.75 mm²
terminations per pole	1
wire strip length	8 mm

model

model	female
connection type	screw connection
connecting thread metric	M16
angle of plug	straight
degree of protection (IP)	IP66/68 (3m;2h) /IP69
thickness of housings (electrical device)	0.5 mm

thickness of housings (electrical device)	8 mm
---	------

material




housing material	polyamide
halogen free	yes
contact material	CuZn
fire load	0.199 kWh/St
insulation components continuous temperature	100 °C
surface finish	silver-plated

dimensions

length	71.2 mm
width	34.6 mm
height	34.6 mm

accessories

item no.	type	description
99.413.6205.2	cover for female connector GL	RST20i3/2 cover piece, for covering unused female connectors, with fastening belt, color light grey
Z5.564.4553.0	cover for female connector GL	RST20i3/2 cover piece, for covering unused female connectors, color light grey

1	2	3	4	5	6				
A	B	C	D	E	F				
A	B	C	D	E	F				
<p>These dimensions will be especially checked at delivery</p> <p>Only inspection dimensions</p> <p>With /E marked dimensions are only valid for internal use</p>			<p>Diese Maße werden bei Abnahme besonders geprüft</p> <p>Ausschließlich Prüfmaße</p> <p>Mit /E gekennzeichnete Maße sind nur für interne Zwecke gültig</p>						
			<p>Auslieferungszustand</p> <p>delivery status</p>  						
<p>Verpackungseinheit: je 100 Stück</p> <p>packaging unit: per 100</p>			<p>96.031.6153.1 RST2013S B1 M03 SW schwarz /black</p> <p>96.031.6153.0 RST2013S B1 M03 GL lichtgrau /lightgrey</p> <p>Bestellnummer /Order number Typ /Type Farbe /color</p> <p>Weitere Daten siehe KATALOG oder eCatalog. Additional data see CATALOG or eCatalog. www.wieland-electric.com eshop.wieland-electric.com</p>						
<p>Offnungsmassbild siehe 96.031.2153.1 14K</p> <p>opening dimension see 96.031.2153.1 14K</p>			<p>Tolerierung Size ISO 14405(E)/Tolerance system Size ISO 14405(E). (This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).</p> <p>ja/yes ☒ Stoffverbots- und Deklarationsliste nach MN 5020.010 ist einzuhalten. Conformity with Wieland document MN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!</p> <p>Freitoleranz nach General tolerance CAD - Zeichnung, keine manuellen Änderungen CAD - drawing, no manual modifications allowed 1. Verwendung: - First Use: - Blatt: 1 von 1 Sheet: 1 of 1</p> <p>Zeichnung Nr./Drawing No. Index</p> <p>96.031.6153.0 13K</p> <p>Maße in mm/Dimensions are in mm</p> <p>Ersatz für/Replacement for: -</p> <p>Type Benennung/Title</p> <p>BUCHSENTE IL female connector</p> <p>wieland www.wieland-electric.com</p> <p>Index Datum / Blatt Date / Sheet Änderung/Revision</p>						
960316153013K_1 CADW3034 HoffmannT 2015-07-24T13:43:53 1.000			QU-MEE-01/14 -						