

product data sheet

item no. 96.223.5092.4

cable assembly RST20I2K1BS325OL 50BR0

RST® CLASSIC connecting cable, female - male, number of poles 2, rated voltage 50 V / 120 V, rated current 20 A, cable type Ölflex® Classic 110, total length 5 m, nominal cross section conductor 2.5 mm², color of coding/ contact carrier signal brown



item no.	96.223.5092.4
EAN	4015573966031
order unit	10 piece(s)

certificates / approvals



technical data

note

note	The total length may vary up to + / - 3 %.
------	--

general

rated current	20 A
rated voltage	50 V / 120 V
rated impulse voltage	4 kV
pollution degree	3
continuity resistor	35.3 mOhm
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	signal brown
Pole codification	1, 2
color of housing inclusive strain relief	black

model

type of construction	shrinkage tube
connection type	crimp
nominal cross section conductor	2.5 mm²
degree of protection (IP)	IP66/68 (3m;2h)
cable type	Ölflex® Classic 110
cable color	grey
cable diameter min.	8.5 mm
cable diameter max.	9.4 mm
version of cable	female - male
type of cord set	connecting cable
version cable end 1	female

version cable end 2	male
shielded	no

material

surface finish	silver-plated
halogen free	no
continuous temperature of cable	70 °C
insulation components continuous temperature	100 °C
fire load	2.498 kWh/St

dimensions

total length	5 m
--------------	-----

